

### ShrinKit 321-A

#### Features and Benefits

ShrinKit 321-A is dual wall heat shrink tubing with a 3:1 ratio. The inner wall melts when heated and is forced into gaps. The attractive and reusable kit is ideal for assembling and identification. When the tubing cools down the adhesive forms a seal against the moisture and protects components. The black tubes are mainly used for the protection of connectors and splices, the clear tubing is ideal for the protection of printed label markers. ShrinKit 321-A covers a wide range of applications due to its ideal 3:1 shrink ratio.

#### Content

This kit contains a range of general purpose tubing lengths clearly sorted. Four different sizes are included in black and clear.



ShrinKit 321-A: permanent protection of identification solutions.

#### Material Data

Material	<b>Polyolefin, Cross-linked (POX)</b>
Shrink Ratio	<b>3:1</b>
Longitudinal change after shrinkage	<b>+1%/-15% max.</b>
Minimum Shrink Temperature	<b>+110 °C</b>
Operating Temperature	<b>-55 °C to +110 °C</b>
Dielectric Strength	<b>11,8 kV/mm according to ASTM D 2671</b>
Flammability	<b>self-extinguishing outer wall (black only)</b>



ShrinKit 321-A.

#### Technical Table

Article-No.	Comp.	Supplied Ø D	Recov. Ø d	Length (L)	Colour	Number of tubes
380-03003 ShrinKit 321-A	1	24	8	200	Black (BK)	5
	2	12	4	65	Transparent (CL)	15
Pack Cont.	3	6	2	50	Black (BK)	20
	3	6	2	50	Transparent (CL)	20
	4	12	4	65	Black (BK)	15
	5	3	1	50	Black (BK)	50
	5	3	1	50	Transparent (CL)	50
	6	6	2	35	Black (BK)	30
	6	6	2	35	Transparent (CL)	30
	7	24	8	200	Transparent (CL)	5
	8	12	4	100	Black (BK)	15
	9	12	4	100	Black (BK)	15
	10	12	4	100	Transparent (CL)	15
11	3	1	40	Black (BK)	50	
11	3	1	40	Transparent (CL)	50	

**New: With Adhesive**

All dimensions in mm. Subject to technical changes.