



SAFETY DATA SHEET EVO-STIK GP AEROSOL

According to Regulation (EC) No 1907/2006

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name EVO-STIK GP AEROSOL
Product No. 132504

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Supplier BOSTIK LIMITED
COMMON ROAD
STAFFORD
STAFFORDSHIRE
ST16 3EH
+44 1785 272625
sds.uk@bostik.com

1.4. Emergency telephone number

+44 1785 272650 (24 Hours)

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)
Physical and Chemical Hazards Flam. Aerosol 1 - H222
Human health Carc. 2 - H351
Environment Not classified.
Classification (1999/45/EEC) Carc. Cat. 3;R40. F+;R12.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

2.2. Label elements

Contains DICHLOROMETHANE
Label In Accordance With (EC) No. 1272/2008



Signal Word Danger
Hazard Statements

H222 Extremely flammable aerosol.
H351 Suspected of causing cancer.

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P211 Do not spray on an open flame or other ignition source.
P251 Pressurized container: Do not pierce or burn, even after use.
P281 Use personal protective equipment as required.
P302+350 IF ON SKIN: Gently wash with plenty of soap and water.

EVO-STIK GP AEROSOL

P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P314	Get medical advice/attention if you feel unwell.
P410+412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F.
P501	Dispose of contents/container in accordance with local regulations.
Supplementary Precautionary Statements	
P201	Obtain special instructions before use.
P202	Do not handle until all safety precautions have been read and understood.
P304+341	IF INHALED: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.
P308+313	IF exposed or concerned: Get medical advice/attention.
P332+313	If skin irritation occurs: Get medical advice/attention.
P337+313	If eye irritation persists: Get medical advice/attention.
P405	Store locked up.

2.3. Other hazards

Pressurised container. Protect from sunlight and do not expose to temperatures exceeding 50C. Do not pierce or burn even after use. Do not spray on a naked flame or any incandescent material - NO SMOKING.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

BUTANE	30-60%
CAS-No.: 106-97-8	EC No.: 203-448-7
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12
BUTANONE	< 1%
CAS-No.: 78-93-3	EC No.: 201-159-0
	Registration Number: 01-2119457290-43
Classification (EC 1272/2008) Flam. Liq. 2 - H225 EUH066 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R66 R67
DICHLOROMETHANE	10-30%
CAS-No.: 75-09-2	EC No.: 200-838-9
Classification (EC 1272/2008) Carc. 2 - H351	Classification (67/548/EEC) Carc. Cat. 3;R40

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Remove victim immediately from source of exposure. Move the exposed person to fresh air at once. Get medical attention.

Ingestion

DO NOT induce vomiting. Get medical attention immediately.

EVO-STIK GP AEROSOL

Skin contact

Promptly wash contaminated skin with soap or mild detergent and water. Promptly remove clothing if soaked through and wash as above. Get medical attention if irritation persists after washing.

Eye contact

Rinse the eye with water immediately. Continue to rinse for at least 15 minutes and get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

4.3. Indication of any immediate medical attention and special treatment needed

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

Fire can be extinguished using: Foam, carbon dioxide or dry powder.

5.2. Special hazards arising from the substance or mixture

Unusual Fire & Explosion Hazards

Aerosol cans may explode in a fire.

Specific hazards

Toxic gases/vapours/fumes of: Carbon dioxide (CO₂). Carbon monoxide (CO).

5.3. Advice for firefighters

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact. Ensure adequate ventilation. Wear personal protective equipment. Wear self contained breathing apparatus.

6.2. Environmental precautions

6.3. Methods and material for containment and cleaning up

Provide ventilation and confine spill. Do not allow runoff to sewer. Absorb in vermiculite, dry sand or earth and place into containers.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Flammable/combustible - Keep away from oxidisers, heat and flames. Ground container and transfer equipment to eliminate static electric sparks. Store at moderate temperatures in dry, well ventilated area.

Storage Class

Flammable liquid storage.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

EVO-STIK GP AEROSOL

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
BUTANE	WEL	600 ppm	1450 mg/m ³	750 ppm	1810 mg/m ³	
BUTANONE	WEL	200 ppm(Sk)	600 mg/m ³ (Sk)	300 ppm(Sk)	899 mg/m ³ (Sk)	
DICHLOROMETHANE	WEL	100 ppm(Sk)	350 mg/m ³ (Sk)	300 ppm(Sk)	1060 mg/m ³ (Sk)	

WEL = Workplace Exposure Limit.

Ingredient Comments

WEL = Workplace Exposure Limits

8.2. Exposure controls

Protective equipment



Engineering measures

Explosion-proof general and local exhaust ventilation.

Respiratory equipment

Respiratory protection must be used if air contamination exceeds acceptable level. Wear mask supplied with: Gas cartridge suitable for organic substances.

Hand protection

Protective gloves must be used if there is a risk of direct contact or splash. Use protective gloves made of: Nitrile.

Eye protection

Wear splash-proof eye goggles to prevent any possibility of eye contact.

Other Protection

Wear appropriate clothing to prevent repeated or prolonged skin contact.

Hygiene measures

Wash promptly if skin becomes contaminated. Wash hands at the end of each work shift and before eating, smoking and using the toilet.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Aerosol.
Colour	Clear
Odour	Chlorinated hydrocarbons.
Solubility	Slightly soluble in water. Soluble in: Chlorinated Hydrocarbons
Initial boiling point and boiling range (°C)	40
Relative density	1.22
Flash point (°C)	- 40
Comments	Can pressure 70psi

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

10.2. Chemical stability

Avoid Heat, sparks, flames.

10.3. Possibility of hazardous reactions

10.4. Conditions to avoid

EVO-STIK GP AEROSOL

10.5. Incompatible materials

Materials To Avoid

Strong alkalis. Strong acids. Strong oxidising substances.

10.6. Hazardous decomposition products

Fire creates: Toxic gases/vapours/fumes of: Carbon monoxide (CO). Carbon dioxide (CO₂). Phosgene (COCl₂). Hydrogen chloride (HCl). Chlorine. Slow hydrolysis with water forms hydrochloric acid

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Other Health Effects

Carcinogen Category 3.

Inhalation

Harmful by inhalation.

Ingestion

May cause discomfort if swallowed.

Skin contact

Prolonged contact may cause dryness of the skin. May cause sensitisation by skin contact.

Eye contact

Spray and vapour in the eyes may cause irritation and smarting.

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment. However, contamination of the aquatic or terrestrial environments should be avoided

12.1. Toxicity

12.2. Persistence and degradability

12.3. Bioaccumulative potential

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

12.6. Other adverse effects

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

14.1. UN number

UN No. (ADR/RID/ADN) 1950

UN No. (IMDG) 1950

UN No. (ICAO) 1950

14.2. UN proper shipping name

EVO-STIK GP AEROSOL

14.3. Transport hazard class(es)

ADR/RID/ADN Class	2.1
ADR/RID/ADN Class	Class 2: Gases
ADR Label No.	2.1 & 6.1
IMDG Class	2.1
ICAO Class/Division	2.1
ICAO Subsidiary risk	6.1
Transport Labels	



14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant
No.

14.6. Special precautions for user

EMS	F-D, S-U
Tunnel Restriction Code	(D)

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716). Control of Substances Hazardous to Health.

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations. Guidance Notes

CHIP for everyone HSG(108). Workplace Exposure Limits EH40. Introduction to Local Exhaust Ventilation HS(G)37.

EU Legislation

Dangerous Substance Directive 67/548/EEC. Dangerous Preparations Directive 1999/45/EC. Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

15.2. Chemical Safety Assessment

SECTION 16: OTHER INFORMATION

General information

This product should be used as directed by Bostik Ltd. For further information consult the product data sheet or contact Technical Services. Information Sources

This safety data sheet was compiled using current safety information supplied by distributor of raw materials.

EVO-STIK GP AEROSOL

Revision Comments

NOTE: Lines within the margin indicate significant changes from the previous revision. This safety data sheet supersedes all previous issues and users are cautioned to ensure that it is current. Destroy all previous data sheets and if in doubt contact Bostik Limited.

Issued By Approved EC
Revision Date Oct 2014
Revision 10
Date December 2003

Risk Phrases In Full

R12 Extremely flammable.
R11 Highly flammable
R36 Irritating to eyes.
R40 Limited evidence of a carcinogenic effect.
R66 Repeated exposure may cause skin dryness or cracking.
R67 Vapours may cause drowsiness and dizziness.

Hazard Statements In Full

EUH066 Repeated exposure may cause skin dryness or cracking.
H220 Extremely flammable gas.
H222 Extremely flammable aerosol.
H225 Highly flammable liquid and vapour.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.
H351 Suspected of causing cancer.