


A Inter Chip-USB Voltage Level Translator

Check for Samples: [TXS0202](#)

FEATURES

- **No Direction Control Signal Required**
- **V_{CCA}, V_{CCB} Supply Voltage: 1.65 V to 3.6 V**
- **Meets All Requirements of the IC-USB Standard**
- **Small Packages: WCSP**
- **Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II**
- **I_{off} Supports Partial-Power-Down Mode Operation**
- **ESD Performance**
 - **A port (Host-Side)**
 - **2000-V Human-Body Model**
 - **100-V Machine Model**
 - **500-V Charged-Device Model**
 - **B port (Peripheral-Side)**
 - **>4kV HBM**


Table 1. YZP TERMINAL ASSIGNMENTS (Top Through View)

	1	2
A	D+(B)	D–(B)
B	GND	V _{CCB}
C	V _{CCA}	OE
D	D+(A)	D–(A)

DESCRIPTION

The TXS0202 is a 2-bit voltage level translator optimized for use in Interchip USB (IC-USB) applications. V_{CCA} and V_{CCB} can each operate over the full range of 1.65 V to 3.6 V. The device has been designed to maintain cross-over skew to be less than 1 ns. The device has integrated pull-ups and pull-down resistors to aid in the protocol communication between a host and a peripheral. The translator is a buffered auto-direction sensing type translator. When the output-enable (OE) input is low, all outputs are placed in the high-impedance state.

This device is fully specified for partial-power-down applications using I_{off}. The I_{off} circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down. To ensure the high-impedance state during power up or power down, OE should be tied to GND through a pull-down resistor; the minimum value of the resistor is determined by the current-sourcing capability of the driver.

ORDERING INFORMATION⁽¹⁾

T _A	PACKAGE ⁽²⁾		ORDERABLE PART NUMBER	TOP-SIDE MARKING
–40°C to 85°C	WCSP – YZP	Tape and reel	TXS0202YZPR	___7PS_ ⁽³⁾

(1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.

(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.

(3) YZP: The actual top-side marking has three preceding characters to denote year, month, and sequence code, and one following character to designate the wafer fab/assembly site.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

TYPICAL APPLICATION BLOCK DIAGRAM



PIN FUNCTIONS

PIN		DESCRIPTION
WSCP (YFP) BALL NO.	NAME	
A1	D+(B)	USB data signal connected to peripheral
A2	D-(B)	USB data signal connected to peripheral
B1	GND	Ground
B2	V _{CCB}	B-side supply voltage (1.65 V to 3.6 V)
C1	V _{CCA}	A-side supply voltage (1.65 V to 3.6 V)
C2	OE	Output enable input control
D1	D+(A)	USB data signal connected to host
D2	D-(A)	USB data signal connected to host

FUNCTIONAL TABLE

CONTROL INPUT	OUTPUT CIRCUIT	OPERATION
OE	B PORT	
L	Hi-Z	Isolation
H	Enabled	Bi-directional communications between host and peripheral

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V_{CCA} V_{CCB}	Supply voltage rang	-0.5	4.6	V
V_I	Input voltage range	A port, B port, control inputs		V
V_O	Voltage range applied to any output in the high-impedance or power-off state	A port, B port		V
I_{IK}	Input clamp current	$V_I < 0$	-50	mA
I_{OK}	Output clamp current	$V_O < 0$	-50	mA
I_{CC} I_{GND}	Continuous current through V_{CCA} , V_{CCB} , or GND		±100	mA
T_{stg}	Storage temperature range	-65	150	°C

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

THERMAL INFORMATION

THERMAL METRIC ⁽¹⁾		TXS0202	UNITS
		YZP	
		8 PINS	
θ_{JA}	Junction-to-ambient thermal resistance	102	°C/W

- (1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report, [SPRA953](#).

RECOMMENDED OPERATING CONDITIONS

		MIN	MAX	UNIT
V_{CCA} , V_{CCB}	Supply voltage	1.65	3.6	V
V_{IH}	High-level input voltage	A port I/Os	$V_{CCA} - 0.2$	V_{CCA}
		B port I/Os	$V_{CCB} - 0.2$	V_{CCB}
		OE	$V_{CCA} \times 0.65$	3.6
V_{IL}	Low-level input voltage	A port I/Os	0	0.15
		B port I/Os	0	0.15
		OE	0	$V_{CCA} \times 0.35$
$\Delta t/\Delta v$	Input transition rise or fall rate		10	ns/V
T_A	Operating free-air temperature	-40	85	°C




Figure 1. Block Diagram Showing Different Modes in the TXS0202

ELECTRICAL CHARACTERISTICS



PARAMETER	TEST CONDITIONS	V _{CCA}	V _{CCBx}	T _A = 25°C	T _A = –40°C to 85°C		UNIT
				TYP	MIN	MAX	
V _{OH(D–)} (D– A or B port)	I _{OH} = –20 μA, V _{Ix} ≥ V _{CCx} – 0.2 V	1.65 V	1.65 V		V _{CCO} × 0.67		V
		2.3 V	2.3 V		V _{CCO} × 0.67		
		3.3 V	3.3 V		V _{CCO} × 0.67		
V _{OL(D–)} (D– A or B port)	I _{OL} = 220 μA, V _{Ix} ≤ 0.15 V	1.65 V	1.65 V		0.45		V
		2.3 V	2.3 V		0.55		
		3.3 V	3.3 V		0.7		
V _{OH(D+)} (D+ A or B port)	I _{OH} = –20 μA, V _{Ix} ≥ V _{CCx} – 0.2 V	1.65 V	1.65 V		V _{CCO} × 0.67		V
		2.3 V	2.3 V		V _{CCO} × 0.67		
		3.3 V	3.3 V		V _{CCO} × 0.67		
V _{OL(D+)} (D– A or B port)	I _{OL} = 220 μA, V _{Ix} ≤ 0.15 V	1.65 V	1.65 V		0.45		V
		2.3 V	2.3 V		0.55		
		3.3 V	3.3 V		0.7		
I _I	OE	1.65 V to 3.6 V	1.65 V to 3.6 V	±2	±2		μA
	D–/D+ A or B port, OE = OPEN			±2	±2		
	I _{BOFF} , D+, D– B port	1.65 V to 3.6 V	0 V		±2		
	I _{AOFF} , D+, D– A port	0 V	1.65 V to 3.6 V		±2		
I _{CCA}	V _I = V _O = Open, OE = High	1.65 V to 3.6 V	1.65 V to 3.6 V	2.2	12		μA
		3.6 V	0 V	2.3	12		
		0 V	3.6 V	0.026	–1		
I _{CCB}	V _I = V _O = Open, OE = High	1.65 V to 3.6 V	1.65 V to 3.6 V	2.7	24		μA
		3.6 V	0 V	0.031	–12		
		0 V	3.6 V	2.7	24		
C _i	OE	3.6 V	3.6 V	2.5	3.5		pF
C _{io}	A port	3.6 V	3.6 V	7	7.5		pF
	B port			9.5	10		

SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range, $V_{CCA} = 1.8 \text{ V} \pm 0.15 \text{ V}$ (unless otherwise noted)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	$V_{CCB} = 1.8 \text{ V} \pm 0.15 \text{ V}$	$V_{CCB} = 3.3 \text{ V} \pm 0.3 \text{ V}$	UNIT
			TYP	TYP	
t_{pd}	A	B	5	5	ns
	B	A	5	5	
t_{rA}	A port rise times		2	2	ns
t_{fA}	A port fall times		2	2	ns
t_{rB}	B port rise times		2	2	ns
t_{fB}	B port fall times		2	2	ns
$t_{sk(o)}$	Channel-to-channel		0.5	0.5	ns
Max data rate			15	15	Mbps

PARAMETER MEASUREMENT INFORMATION



VOLTAGE WAVEFORMS
PROPAGATION DELAY TIMES

DATA RATE, SKEW, PROPAGATION DELAY,
OUTPUT RISE AND FALL TIME MEASUREMENT

- A. C_L includes probe and jig capacitance.
- B. The outputs are measured one at a time, with one transition per measurement.
- C. t_{PLH} and t_{PHL} are the same as t_{pd} .

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TXS0202YZPR	ACTIVE	DSBGA	YZP	8	3000	Green (RoHS & no Sb/Br)	SNAGCU	Level-1-260C-UNLIM	-40 to 85	7P	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "-" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION



QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TXS0202YZPR	DSBGA	YZP	8	3000	180.0	8.4	1.02	2.02	0.63	4.0	8.0	Q1

TAPE AND REEL BOX DIMENSIONS




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TXS0202YZPR	DSBGA	YZP	8	3000	182.0	182.0	20.0

YZP (R-XBGA-N8)

DIE-SIZE BALL GRID ARRAY



- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
 - B. This drawing is subject to change without notice.
 - C. NanoFree™ package configuration.

NanoFree is a trademark of Texas Instruments.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com