



Main

Range	ClimaSys CV
Category	Fan
Type of filter	Standard
Flow rate	Free flow rate with standard filter : 350 m ³ /h at 60 Hz Free flow rate with standard filter : 300 m ³ /h at 50 Hz
[Us] rated supply voltage	75...126 V
Input voltage	115 V 50/60 Hz

Complementary

Absorbed power	36 W 60 Hz 36 W 50 Hz
[In] rated current	0.32 A 60 Hz 0.35 A 50 Hz
Noise level < at	55...56 dB
Bearing type	Ball
Height	External : 268 mm
Width	External : 248 mm
Depth	External : 116 mm
Cut-out dimensions	223 x 223 mm
Product weight	1.3 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille : grey RAL 7035
Ambient air temperature for operation	-10...70 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	158 Pa flow rate 0 m ³ /h
Connections - terminals	Faston connector
IP degree of protection	IP54
Device composition	1 power cord 1 cut-out template 1 outlet grille front 1 filter front of axial motor 2 protective grille on the front and rear surfaces 1 axial motor
Condition of use	Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations