

YY Unshielded Multicore PVC Flexible Control Cable

pro-POWER



RoHS
Compliant

Application:

Used as interconnecting cable for measuring, controlling or regulation in control equipment for assembly and production lines, conveyors and for computer units. Suitable for fixed installations or for flexible use in conditions of light mechanical stress. Can be used outdoors when protected against direct sunlight, and in dry or moist conditions indoors.

Construction:

Conductor:

Class 5 flexible copper conductor according to BS EN 60228
(previously BS 6360)

Insulation:

PVC (Polyvinyl Chloride) T12 according to BS EN 50363

Sheath:

PVC (Polyvinyl Chloride) TM2 according to BS EN 50363

Cable Standards

Made in accordance with the following:

Generally to BS EN 50525-2-11 (previously BS 6500) and VDE 0250, BS EN/IEC 60332-1

Characteristics:

Voltage Rating (Uo/U)

300/500V

Temperature Rating:

Fixed : -40°C to +70°C

Flexed : -5°C to +70°C

Min. Bending Radius:

Fixed : 4 × overall diameter

Flexed : 12.5 × overall diameter

Core Identification:

Coloured Cores:

3 core : Green/Yellow, Blue and Brown

4 core : Green/Yellow, Brown, Black and Grey

5 core : Green/Yellow, Brown, Black, Grey and Blue

Sheath Colour:

Grey

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER

YY Unshielded Multicore PVC Flexible Control Cable



Dimensions:

Part Number	No. of Cores	Nominal Cross Sectional Area mm ²	Nominal Overall Diameter mm	Nominal Weight kg/km
PP001167	3	1.5	7.54	95
PP001168		2.5	9.04	144
PP001169	4	1.5	8.23	117
PP001170		2.5	9.87	178
PP001171	5	2.5	11.05	213

Conductors

Class 5 Flexible Copper Conductors for Multi-Core Cables

Nominal Cross Sectional Area mm ²	Max. Diameter of Wires in Conductor mm	Max. Resistance of Conductor at 20°C Plain Wires Ω / km
1.5	0.26	13.3
2.5	0.26	7.98

The above table is in accordance with BS EN 60228 (previously BS 6360)

Electrical Characteristics:

Current Carrying Capacity at 30°C

Nominal Cross Sectional Area mm ²	Current Rating Amps
1.5	18
2.5	26

The above table is a guide extracted from DIN VDE 0298 Part 4 and DIN 0100 Part 430

De-Rating Factors:

No. of Cores	5
De-Rating Factor	0.75

Part Number Table

Description	Reel Length	Part Number
YY Multicore Cable, 3 Core, 1.5mm ²	50m	PP001167
YY Multicore Cable, 3 Core, 2.5mm ²		PP001168
YY Multicore Cable, 4 Core, 1.5mm ²		PP001169
YY Multicore Cable, 4 Core, 2.5mm ²		PP001170
YY Multicore Cable, 5 Core, 2.5mm ²		PP001171

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.