

NYY-J Unshielded Multicore FR-PVC Power and Control Cable

pro-POWER

RoHS
Compliant



Application:

Power and control cable for fixed installation. Can be used indoors, outdoors, underground, in concrete and in water.

Construction:

Conductor:

Class 1 solid copper conductor according to BS EN 60228
(previously BS 6360)

Insulation:

PVC (Polyvinyl Chloride)

Filler:

PVC (Polyvinyl Chloride)

Sheath:

FR-PVC (Flame Retardant - Polyvinyl Chloride)

Cable Standards

Made in accordance with the following:
BS EN/IEC 60502-1, BS EN/IEC 60332-1-2

Characteristics:

Voltage Rating (U_o/U)

600/1000V

Temperature Rating:

Fixed : -15°C to +70°C

Flexed : -5°C to +50°C

Min. Bending Radius:

Fixed : 12 × overall diameter

Core Identification:

Up to and including 5 core: colour coded or number coded

Sheath Colour:

Black

NYY-J Unshielded Multicore FR-PVC Power and Control Cable

pro-POWER

Dimensions:

Part Number	No. of Cores	Nominal Cross Sectional Area mm ²	Nominal Thickness of Insulation mm	Nominal Thickness of Sheath mm	Nominal Overall Diameter mm	Nominal Weight kg/km
PP001064	3	1.5	0.8	1.8	10.4	166
PP001065		2.5	0.8		11.3	212
PP001066		4	1		13.1	299
PP001067	4	1.5	0.8		11.6	198
PP001068		2.5	0.8		12.1	252
PP001069		4	1		14	355
PP001070		6	1		15.4	465
PP001071	5	1.5	0.8		12	232
PP001072		2.5	0.8		13.1	302
PP001073		4	1		15.2	428

Conductors

Class 1 Solid Conductors for Multi-Core Cables

Nominal Cross Sectional Area mm ²	Max. Resistance of Conductor at 20°C Circular, Annealed Copper Conductor Plain Wires Ω / km
1.5	12.1
2.5	7.41
4	4.61
6	3.08

Electrical Characteristics:

Current Carrying Capacity

No. of Cores	Nominal Cross Sectional Area mm ²	Current Carrying Capacity	
		In Duct Amps	In Air Amps
3	1.5	26	18
	2.5	34	25
	4	44	34

NYY-J Unshielded Multicore FR-PVC Power and Control Cable



No. of Cores	Nominal Cross Sectional Area mm ²	Current Carrying Capacity	
		In Duct Amps	In Air Amps
4	1.5	26	18
	2.5	34	25
	4	44	34
	6	56	43
5	1.5	24	18
	2.5	34	25
	4	44	34

Ambient Temperature : 30°C
 Depth of Laying : 0.5m
 Ground Temperature : 15°C
 Thermal Resistivity of Soil : 12km/w

De-Rating Factors:

For Air Temperature other than 30°C

Air Temperature	20°C	25°C	30°C	35°C	40°C	45°C	50°C
De-Rating Factor	1.12	1.07	1	0.94	0.87	0.79	0.71

Part Number Table

Description	Reel Length	Part Number
NYY-J Multicore Cable, 3, 1.5mm ²	50m	PP001064
NYY-J Multicore Cable, 3, 2.5mm ²		PP001065
NYY-J Multicore Cable, 3, 4mm ²		PP001066
NYY-J Multicore Cable, 4, 1.5mm ²		PP001067
NYY-J Multicore Cable, 4, 2.5mm ²		PP001068
NYY-J Multicore Cable, 4, 4mm ²		PP001069
NYY-J Multicore Cable, 4, 6mm ²		PP001070
NYY-J Multicore Cable, 5, 1.5mm ²		PP001071
NYY-J Multicore Cable, 5, 2.5mm ²		PP001072
NYY-J Multicore Cable, 5, 4mm ²		PP001073

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

