

Bench Type Digital Multimeter



Description

This model is a auto ranging digital bench-type multimeter with average value display, full function and full range overload protection and a unique outlook design. It can be powered by AC 220V/50Hz or 1.5V Cell (R14) × 6. It is a ideal testing meter with superior performance. This model is widely used in industrial production and service, technological research and design, college education (laboratory, courses), and automotive industry.



Features

- Display Count : 6,000
- Auto Range
- Bandwidth (Hz) : 100kHz
- Diode Test
- Auto Power Off
- Transistor Test
- Continuity Buzzer
- Low Battery Indication
- Data Hold
- MAX/MIN
- RS-232
- USB Interface
- LCD Backlight
- Input Protection
- Input Impedance for DCV : 600mV Range : Around 3GΩ,
All Other Ranges : Around 10MΩ
- Voltage & Current : AC + DC Measurement

Specifications

	Range	Accuracy
DC Voltage (V)	600mV/6V/60V/600V/1000V	±(0.3%+2)
AC Voltage (V)	600mV/6V/60V/600V/1000V	±(0.6%+5)
DC Current (A)	600μA/6000μA/60mA/600mA/10A	±(0.5%+3)
AC Current (A)	600μA/6000μA/60mA/600mA/10A	±(1%+5)
Resistance (Ω)	600Ω/6kΩ/60kΩ/600kΩ/6MΩ/60MΩ	±(0.5%+2)
Capacitance (F)	6nF/60nF/600nF/6μF/60μF/600μF/6mF	±(2%+5)
Frequency (Hz)	6kHz/60kHz/600kHz/6MHz/60MHz	±(0.1%+3)
Temperature (°C)	-40°C to 1000°C	±(1%+3)
Temperature (°F)	-40°F to 1832°F	±(1.5%+5)

General Characteristic

Power	AC 220V/50Hz or 1.5V Cells (R14) ×6
LCD Size	128mm ×28mm
Product Color	Orange and Grey
Product Net Weight	2.4 Kg
Product Size	310mm × 240mm × 105mm
Standard Accessories	Test Lead, AC 220V Power Cord, Software, RS-232 Interface Cable, USB Interface Cable, Alligator Clip, Point Contact Temperature Probe, Multi-Purpose Socket
Safety Rating	CATII 1000V

Part Number Table

Description	Part Number
Bench Type Digital Multimeter	72-1016

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

