



Item # LR2K0310, TeSys K IEC Overload Relay

TeSys K IEC Overload Relay

Specifications

Type	TeSys K IEC Bi-Metallic Overload Relay
For Use With Contactors	TeSys K AC or DC IEC Contactor
Ambient Compensated Bimetallic	Yes
Class 10	Yes
Single Phase Sensitivity	Yes
Current Setting Range	2.6A to 3.7A
Termination Method	Screw Clamp
Power Wire Size (External Lug Size)	#12 - #18 AWG
Control Wire Size (External Lug Size)	#12 - #18 AWG
Control Terminal Torque	#12 - #18 AWG
Power Terminal Torque	7 lb-in (0.8 Nm)
Mounting Directly to Contactor	Yes
Mounting Separate from Contactor	LA7K0064
Weight	0.35 lb (0.13 kg)
UL File/CCN	E164353 / NKCR
CSA File	LR43364 3211 03
Meets Standard	IEC 60947
CE	Yes
RoHS	Yes