

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [**0191600009**](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 12-22 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Splices
 Series [19160](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 MolexKits Yes
 Overview [Splices](#)
 Product Name Closed-End Insulated
 UPC 800753110182

Physical

Barrel Type Closed
 Color - Resin Natural
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.689g
 Packaging Type Bag
 Temperature Range - Operating 105°C
 Wire Insulation Diameter 6.86mm max.
 Wire Size AWG 12, 14, 16, 18, 20, 22

Electrical


Voltage - Maximum 600V

Material Info

Old Part Number NC-2212

Reference - Drawing Numbers

Packaging Specification PK-19408-109
 Product Specification PS-19902-013
 Sales Drawing SD-19160-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014
 December 17): No

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[19160 Series](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

| Description | Product # |
|--|----------------------------|
| Hand Crimp Tool | 0640010900 |
| Crimp Head for the AT-200™ Pneumatic Hand Tool | 0640050900 |
| Crimp Head for the AT-200™ Pneumatic Hand Tool | 0640053600 |

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION