




marlow industries, inc.®
Subsidiary of II-VI INCORPORATED

TECHNICAL DATA SHEET





RC3-4

Single-Stage Thermoelectric Cooler
RoHS 2002/95/EC Compliant

PERFORMANCE VALUES

Hot Side Temperature (°C)	27°C	50°C
Δ Tmax (°C-dry N ₂):	65	73
Qmax (watts):	9	10
I _{max} (amps):	3.7	3.7
V _{max} (vdc):	3.6	4.1
AC Resistance (ohms):	0.8	---

MECHANICAL CHARACTERISTICS



Ceramic Material: Alumina (AC)

Dimensions in [] are millimeters


ORDERING OPTIONS

Model Number	Description
RC3-4-01	Base Model w/ leads
RC3-4-01L	Lapped Model
RC3-4-01S	Sealed Model
RC3-4-01LS	Lapped and Sealed Model

AVAILABLE MODIFICATIONS

Solid-state reliability.
Built with high temperature solder with the ability to withstand higher assembly processing temperatures for short periods of time (<160°C).
Superior nickel diffusion barriers on elements.
High strength for rugged environment.
Porched configuration for enhanced leadwire strength.
RTV sealing available (Optional).
Lapped option available for multiple module applications.

ENVIRONMENT: ONE ATMOSPHERE DRY NITROGEN



For performance information in a vacuum or with hot side temperatures other than 27°C or 50°C, consult one of our Applications Engineers.

Installation

Recommended mounting methods: Bonding with thermal epoxy or soldering with metallized ceramics. For additional information, please refer to our TEC Installation Guide.

Operation Cautions

For maximum reliability, storage and operation below 85°C in a non-condensing environment is recommended. To minimize thermal stress, use linear/proportional temperature control or a similar method rather than an ON/OFF method.

CONTACT US:

For customer support or general questions please contact a local office below or consult our website for distributor information.

Marlow Industries, Inc.
10451 Vista Park Road
Dallas Texas 75238-1645
214-340-4900 (tel)
214-341-5212 (fax)
www.marlow.com

Marlow Industries Europe GmbH
Im Tiefen See 58
64293 Darmstadt - Germany
Tel.: +49 (0) 6151 8806 -0
Fax.: +49 (0) 6151 8806 9455

II-VI Japan Inc.
WBG Marive East 17F
2-6 Nakase, Mihama-ku
Chiba-Shi, Chiba 261-7117
Japan
81 43 297 2693 (tel)
81 43 297 3003 (fax)
center@ii-vi.co.jp
www.ii-vi.co.jp

II-VI Singapore Pte., Ltd.
Blk. 5012, Techplace II
#04-07 & 05-07/12, Ang Mo Kio Ave. 5
Singapore 569876
(65) 6481 8215 (tel)
(65) 6481 8702 (fax)
info@ii-vi.com.sg
www.ii-vi.com.sg

Marlow Industries China, II-VI
Technologies Beijing
A subsidiary of II-VI Incorporated
Rm 202, 1# Lize 2nd Middle Road
Wangjing, Chaoyang District
Beijing 100102 China
010-64398226 ext 105 (tel)
010-64399315 (fax)
info@iivibj.com