

# SAFETY DATA SHEET

Techspray Wondermask P

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

**Product name** : Techspray Wondermask P  
**Product code** : 2211/CAN/EUR-2SQ, 8SQ, G, 5G, 54G  
**Product description** : Wave solder process masking agent  
**Product type** : Liquid.  
**Other means of identification** : Not available.

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Not applicable.

### 1.3 Details of the supplier of the safety data sheet

Manufacturer  
Techspray, L.P  
1001 N.W. 1st Street  
P.O. Box 949  
Amarillo TX 79107

Distributor

Importer  
ITW Contamination Control BV Saffierlaan 5  
VZ-2132 Hoofddorp  
The Netherlands  
Email: [info@itw-cc.com](mailto:info@itw-cc.com)

Tel: +31 88 1307 400  
FAX: +31 88 1307 499

**e-mail address of person responsible for this SDS** : [info@itw-cc.com](mailto:info@itw-cc.com)

#### National contact

ITW Contamination Control BV  
Saffierlaan 5  
VZ-2132 Hoofddorp  
The Netherlands

Email: [info@itw-cc.com](mailto:info@itw-cc.com)

Tel: +31 88 1307 400  
FAX: +31 88 1307 499

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.4 Emergency telephone number

#### National advisory body/Poison Centre

**Telephone number** : EMERGENCY HEALTH INFORMATION:  
Chemtrec - 1-800-424-9300 or collect 703-527-3887

#### Supplier

**Telephone number** : Chemtrec - 1-800-424-9300 or collect 703-527-3887

**Hours of operation** : 24/7

**Information limitations** : EMERGENCY HEALTH INFORMATION:  
EMERGENCY SPILL INFORMATION:  
Transport information

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

**Product definition** : Mixture

#### Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Not classified.

The product is not classified as hazardous according to Regulation (EC) 1272/2008 as amended.

**Ingredients of unknown toxicity** : 95.5 percent of the mixture consists of component(s) of unknown toxicity

**Ingredients of unknown ecotoxicity** : Contains 95.5 % of components with unknown hazards to the aquatic environment

#### Classification according to Directive 1999/45/EC [DPD]

The product is not classified as dangerous according to Directive 1999/45/EC and its amendments.

**Classification** : Xi; R38  
R43

See Section 16 for the full text of the R phrases or H statements declared above.

See Section 11 for more detailed information on health effects and symptoms.

### 2.2 Label elements

**Signal word** : No signal word.

**Hazard statements** : No known significant effects or critical hazards.

#### Precautionary statements

**Prevention** : Not applicable.

**Response** : Not applicable.

**Storage** : Not applicable.

**Disposal** : Not applicable.

**Supplemental label elements** : Safety data sheet available on request.

**Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.

#### Special packaging requirements

**Containers to be fitted with child-resistant fastenings** : Not applicable.

**Tactile warning of danger** : Not applicable.

## SECTION 2: Hazards identification

### 2.3 Other hazards

**Other hazards which do not result in classification** : None known.

## SECTION 3: Composition/information on ingredients

### 3.2 Mixtures : Mixture

Product/ingredient name	Identifiers	%	Classification		Type
			67/548/EEC	Regulation (EC) No. 1272/2008 [CLP]	
1, 2-Benzenedicarboxylic acid, benzyl C7-9-branched and linear alkyl esters 4-Nonylphenol, branched, ethoxylated	EC: 271-082-5 CAS: 68515-40-2	>=1 - <5	Not classified.	Aquatic Chronic 4, H413	[1]
	EC: 500-315-8 CAS: 127087-87-0	>=1 - <5	Not classified.	Not classified.  <b>See Section 16 for the full text of the H statements declared above.</b>	[5]

There are no additional ingredients present which, within the current knowledge of the supplier, are classified and contribute to the classification of the substance and hence require reporting in this section.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs, vPvBs or Substances of equivalent concern, or have been assigned a workplace exposure limit and hence require reporting in this section.

#### Type

[1] Substance classified with a health or environmental hazard

[2] Substance with a workplace exposure limit

[3] Substance meets the criteria for PBT according to Regulation (EC) No. 1907/2006, Annex XIII

[4] Substance meets the criteria for vPvB according to Regulation (EC) No. 1907/2006, Annex XIII

[5] Substance of equivalent concern

Occupational exposure limits, if available, are listed in Section 8.

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur. In case of inhalation of decomposition products in a fire, symptoms may be delayed. The exposed person may need to be kept under medical surveillance for 48 hours.
- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.
- Ingestion** : Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training.

### 4.2 Most important symptoms and effects, both acute and delayed

#### Potential acute health effects

## SECTION 4: First aid measures

- Eye contact** : This product may irritate eyes upon contact. May cause eye irritation.
- Inhalation** : Exposure to decomposition products may cause a health hazard. Serious effects may be delayed following exposure.
- Skin contact** : May cause skin irritation.
- Ingestion** : Harmful if swallowed.

### Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following: watering pain or irritation redness
- Inhalation** : Adverse symptoms may include the following: respiratory tract irritation
- Skin contact** : Adverse symptoms may include the following: irritation
- Ingestion** : Adverse symptoms may include the following: nausea or vomiting stomach pains

### 4.3 Indication of any immediate medical attention and special treatment needed

- Notes to physician** : In case of inhalation of decomposition products in a fire, symptoms may be delayed. The exposed person may need to be kept under medical surveillance for 48 hours.
- Specific treatments** : No specific treatment.

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

### 5.2 Special hazards arising from the substance or mixture

- Hazards from the substance or mixture** : In a fire or if heated, a pressure increase will occur and the container may burst.
- Hazardous thermal decomposition products** : Decomposition products may include the following materials:  
carbon dioxide  
carbon monoxide  
nitrogen oxides

### 5.3 Advice for firefighters

- Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Put on appropriate personal protective equipment.
- For emergency responders** : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

## SECTION 6: Accidental release measures

**6.2 Environmental precautions** : Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

### 6.3 Methods and material for containment and cleaning up

**Small spill** : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.

**Large spill** : Stop leak if without risk. Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations. Dispose of via a licensed waste disposal contractor.

**6.4 Reference to other sections** : See Section 1 for emergency contact information.  
See Section 8 for information on appropriate personal protective equipment.  
See Section 13 for additional waste treatment information.

## SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

### 7.1 Precautions for safe handling

**Protective measures** : Put on appropriate personal protective equipment (see Section 8).  
**Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

### 7.2 Conditions for safe storage, including any incompatibilities

Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination.

### 7.3 Specific end use(s)

**Recommendations** : Not available.  
**Industrial sector specific solutions** : Not available.

## SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. Information is provided based on typical anticipated uses of the product. Additional measures might be required for bulk handling or other uses that could significantly increase worker or exposure or environmental releases.

### 8.1 Control parameters

**Occupational exposure limits**  
No exposure limit value known.

## SECTION 8: Exposure controls/personal protection

**Recommended monitoring procedures** : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to monitoring standards, such as the following: European Standard EN 689 (Workplace atmospheres - Guidance for the assessment of exposure by inhalation to chemical agents for comparison with limit values and measurement strategy) European Standard EN 14042 (Workplace atmospheres - Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents) European Standard EN 482 (Workplace atmospheres - General requirements for the performance of procedures for the measurement of chemical agents) Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

### DNELs/DMELs

No DNELs/DMELs available.

### PNECs

No PNECs available

## 8.2 Exposure controls

**Appropriate engineering controls** : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

### Individual protection measures

**Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

**Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.

### Skin protection

**Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

**Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Respiratory protection** : Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

**Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

#### Appearance

Physical state	: Liquid. [gel]
Colour	: Pink/ Red.
Odour	: Not available.
Odour threshold	: Not available.
pH	: Not available.
Melting point/freezing point	: Not available.
Initial boiling point and boiling range	: Not available.
Flash point	: [Product does not sustain combustion.]
Evaporation rate	: Not available.
Flammability (solid, gas)	: Not available.
Upper/lower flammability or explosive limits	: Not available.
Vapour pressure	: Not available.
Vapour density	: Not available.
Relative density	: 1
Solubility(ies)	: Not available.
Partition coefficient: n-octanol/ water	: Not available.
Auto-ignition temperature	: Not available.
Decomposition temperature	: Not available.
Viscosity	: Not available.
Explosive properties	: Not available.
Oxidising properties	: Not available.

### 9.2 Other information

No additional information.

## SECTION 10: Stability and reactivity

10.1 Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
10.2 Chemical stability	: The product is stable.
10.3 Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
10.4 Conditions to avoid	: Avoid all possible sources of ignition (spark or flame).
10.5 Incompatible materials	: Reactive or incompatible with the following materials: acids alkalis oxidizing materials
10.6 Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.



## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
1,2-Benzenedicarboxylic acid, benzyl C7-9-branched and linear alkyl esters	LD50 Dermal	Rabbit	>7940 mg/kg	-
	LD50 Oral	Rat	>15800 mg/kg	-

**Conclusion/Summary** : Not available.

#### Acute toxicity estimates

Route	ATE value
Inhalation (vapours)	160.7 mg/l

#### Irritation/Corrosion

**Conclusion/Summary** : Not available.

#### Sensitisation

**Conclusion/Summary** : Not available.

#### Mutagenicity

**Conclusion/Summary** : Not available.

#### Carcinogenicity

**Conclusion/Summary** : Not available.

#### Reproductive toxicity

**Conclusion/Summary** : Not available.

#### Teratogenicity

**Conclusion/Summary** : Not available.

#### Specific target organ toxicity (single exposure)

Not available.

#### Specific target organ toxicity (repeated exposure)

Not available.

#### Aspiration hazard

Not available.

**Information on the likely routes of exposure** : Not available.

#### Potential acute health effects

- Eye contact** : This product may irritate eyes upon contact. May cause eye irritation.
- Inhalation** : Exposure to decomposition products may cause a health hazard. Serious effects may be delayed following exposure.
- Skin contact** : May cause skin irritation.
- Ingestion** : Harmful if swallowed.

#### Symptoms related to the physical, chemical and toxicological characteristics

- Eye contact** : Adverse symptoms may include the following: watering pain or irritation redness
- Inhalation** : Adverse symptoms may include the following: respiratory tract irritation
- Skin contact** : Adverse symptoms may include the following: irritation
- Ingestion** : Adverse symptoms may include the following: nausea or vomiting stomach pains

#### Delayed and immediate effects and also chronic effects from short and long term exposure

##### Short term exposure



## SECTION 11: Toxicological information

**Potential immediate effects** : Not available.

**Potential delayed effects** : Not available.

### Long term exposure

**Potential immediate effects** : Not available.

**Potential delayed effects** : Not available.

### Potential chronic health effects

Not available.

**Conclusion/Summary** : Not available.

**General** : No known significant effects or critical hazards.

**Carcinogenicity** : No known significant effects or critical hazards.

**Mutagenicity** : No known significant effects or critical hazards.

**Teratogenicity** : No known significant effects or critical hazards.

**Developmental effects** : No known significant effects or critical hazards.

**Fertility effects** : No known significant effects or critical hazards.

**Other information** : Not available.

## SECTION 12: Ecological information

### 12.1 Toxicity

**Conclusion/Summary** : Not available.

### 12.2 Persistence and degradability

**Conclusion/Summary** : Not available.

### 12.3 Bioaccumulative potential

Product/ingredient name	LogP <sub>ow</sub>	BCF	Potential
1,2-Benzenedicarboxylic acid, benzyl C7-9-branched and linear alkyl esters	6.66	155 to 886	high

### 12.4 Mobility in soil

**Soil/water partition coefficient (K<sub>oc</sub>)** : Not available.

**Mobility** : Not available.

### 12.5 Results of PBT and vPvB assessment

**PBT** : Not applicable.

**vPvB** : Not applicable.

**12.6 Other adverse effects** : No known significant effects or critical hazards.

## SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

### 13.1 Waste treatment methods

#### Product

**Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

**Hazardous waste** : Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 91/689/EEC.

#### Packaging

**Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.

**Special precautions** : This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

## SECTION 14: Transport information

	ADR/RID	ADN	IMDG	IATA
14.1 UN number	Not regulated.	Not regulated.	Not regulated.	Not regulated.
14.2 UN proper shipping name	-	-	-	-
14.3 Transport hazard class(es)	-	-	-	-
14.4 Packing group	-	-	-	-
14.5 Environmental hazards	No.	No.	No.	No.
Additional information	-	-	-	-

**14.6 Special precautions for user** : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

**14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code** : Not available.

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### EU Regulation (EC) No. 1907/2006 (REACH)

##### Annex XIV - List of substances subject to authorisation

###### Annex XIV

None of the components are listed.

###### Substances of very high concern

<b>Ingredient name</b>	<b>Intrinsic property</b>	<b>Status</b>	<b>Reference number</b>	<b>Date of revision</b>
4-Nonylphenol, branched and linear, ethoxylated [substances with a linear and/or branched alkyl chain with a carbon number of 9 covalently bound in position 4 to phenol, ethoxylated covering UVCB- and well-defined substances, polymers and homologues, which include any of the individual isomers and/or combinations thereof]	Substance of equivalent concern for environment	Candidate	ED/69/2013	4/15/2013

**Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.

#### Other EU regulations

**Europe inventory** : Not determined.

##### Seveso II Directive

This product is not controlled under the Seveso II Directive.

#### International regulations

##### Chemical Weapon Convention List Schedules I, II & III Chemicals

Not listed.

##### Montreal Protocol (Annexes A, B, C, E)

Not listed.

##### Stockholm Convention on Persistent Organic Pollutants

Not listed.

##### Rotterdam Convention on Prior Inform Consent (PIC)

Not listed.

##### UNECE Aarhus Protocol on POPs and Heavy Metals

Not listed.

#### International lists

##### National inventory

**Australia** : Not determined.

**Canada** : Not determined.

**China** : Not determined.

**Japan** : Not determined.

**Malaysia** : Not determined.

**New Zealand** : Not determined.

**Philippines** : Not determined.

**Republic of Korea** : Not determined.

**Taiwan** : Not determined.

Techspray Wondermask P

## SECTION 15: Regulatory information

**United States** : Not determined.

**15.2 Chemical Safety Assessment** : This product contains substances for which Chemical Safety Assessments are still required.

## SECTION 16: Other information

✔ Indicates information that has changed from previously issued version.

**Abbreviations and acronyms** : ATE = Acute Toxicity Estimate  
CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]  
DMEL = Derived Minimal Effect Level  
DNEL = Derived No Effect Level  
EUH statement = CLP-specific Hazard statement  
PBT = Persistent, Bioaccumulative and Toxic  
PNEC = Predicted No Effect Concentration  
RRN = REACH Registration Number  
vPvB = Very Persistent and Very Bioaccumulative

### Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Classification	Justification
Not classified.	
<b>Full text of abbreviated H statements</b> : H413	May cause long lasting harmful effects to aquatic life.
<b>Full text of classifications [CLP/GHS]</b> : Aquatic Chronic 4, H413	LONG-TERM AQUATIC HAZARD - Category 4

**Full text of abbreviated R phrases** : Not applicable.

**Full text of classifications [DSD/DPD]** : Not applicable.

**Date of printing** : 8/13/2014.

**Date of issue/ Date of revision** : 8/13/2014.

**Date of previous issue** : 8/13/2014.

**Version** : 1.02

### Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.