


HDMI over Cat5/Cat6 Active Extender Kit, Box-Style Transmitter & Receiver for Video and Audio, 1920x1200 at 60Hz/1080p

MODEL NUMBER: **B126-1A1**



Description

The B126-1A1 transmits a 1080p (60Hz) signal to a monitor up to 150 ft. away using Cat5e/6 cable. To achieve maximum distance and resolution, use 24Awg Solid Wire Cat5e/6 cable. (Tripp Lite's N202-Series) The transmitter unit features an HDMI port for the connection of a local monitor. The receiver unit features a built-in Equalization control for adjustment of the video image. Supports 24-bit True Color (8-bits per channel), HDCP, 3D, and both stereo audio and 7.1 channel surround sound audio (*7.1 channel surround sound signal will be Multi-Channel or PCM*).

Installation is simple. Connect the transmitter unit to an HDMI source using a Tripp Lite P568-Series HDMI cable (not included). Connect the receiver unit to a display using a Tripp Lite P568-Series HDMI cable (not included).

Finally, connected the receiver to the RJ45 port on the transmitter using a single Cat5e/6 cable.

- A 1080p (60Hz) signal can be transmitted up to 150 ft.
- A 1080i (60Hz) signal can be transmitted up to 200 ft.
- A 3D signal can be transmitted up to 125 ft.

Further extend the signal range or add more displays by using a Tripp Lite B126-110 Remote Repeater unit:

- Add up to three repeaters, with a receiver unit located at the end of the installation, for a total of 4 displays.
- A 1080p (60Hz) signal can be extended up to 125 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080p (60Hz) signal can be extended up to 500 ft..
- A 1080i (60Hz) signal can be extended up to 175 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080i (60Hz) signal can be extended up to 700 ft..
- A 3D signal can be extended up to 100 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 3D signal can be extended up to 400 ft..

Highlights

- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- HDCP and 3D compatible
- Compatible with both stereo audio and 7.1 channel surround sound audio (*7.1 channel surround sound signal will be Multi-Channel or PCM*)
- Supports 24-bit True Color (8-bits per channel)
- Transmitter unit features an HDMI port for the connection of a local monitor
- Can further expand the range and number of monitors by adding repeaters
- Mounting hardware included
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B126-1A1 local unit
- B126-1A1 remote unit
- Screwdriver for adjustment of Equalization
- (x2) Mounting hardware
- (x2) External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's manual



Features

- Two piece kit includes both local transmitter and remote receiver units
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, is required to achieve maximum distance and resolution.
- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source and monitor.
- HDCP and 3D compatible
- Compatible with both stereo audio and 7.1 channel surround sound audio (*7.1 channel surround sound signal will be Multi-Channel or PCM*)
- Supports 24-bit True Color (8-bits per channel)
- Transmitter unit features an HDMI port for the connection of a local monitor
- Can further expand the range and number of monitors by adding B126-110 repeaters
- Connect up to three repeaters, with a receiver unit located at the end of the installation, for a total of 4 displays.
- A 1080p (60Hz) signal can be extended up to 125 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080p (60Hz) signal can be extended up to 500 ft..
- A 1080i (60Hz) signal can be extended up to 175 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 1080i (60Hz) signal can be extended up to 700 ft..
- A 3D signal can be extended up to 100 ft. for each repeater in the installation. In a full 4 level chain (3 repeaters, 1 receiver), a 3D signal can be extended up to 400 ft..
- Features a built-in Equalization control for adjustment of the video image
- Mounting hardware is included that allows the B126-110 to be rackmounted, wallmounted or pole mounted
- Compatible with all operating systems
- Plug and play; No drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
Display Style	Extender
Cable Type	HDMI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	HDMI (FEMALE) (X3)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connector B	RJ45 (FEMALE) (X2)
Ports	1
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>