



4-Port HDMI over Cat5/Cat6 Extender Splitter, Box-Style Transmitter for Video and Audio, 1920x1200 1080p at 60Hz

MODEL NUMBER: **B126-004**



Description

The B126-004 transmits a 1080p(60Hz) signal to four monitors up to 150 ft. away using Cat5e/6 cable, making it the ideal for digital signage applications ranging from retail and point-of-sale displays to trade show presentations. To achieve maximum distance and resolution, use 24Awg Solid Wire Cat5e/6 cable. (Tripp Lite's N202-Series) Daisychain up to three B126-004 transmitters to connect up to 13 monitors(1 Local, 12 Remote). Supports 24-bit True Color(8-bits per channel), HDCP, 3D, and both stereo audio and 7.1 channel surround sound audio(7.1 channel surround sound signal will be Multi-Channel or PCM). Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases.

Installation Description

Installation is simple. Connect the B126-004 transmitter to an HDMI source using a Tripp Lite P568-Series HDMI cable(not included). Connect a Tripp Lite B126-series receiver(not included) to each display using a Tripp Lite P568-Series HDMI cable(not included). Finally, each remote receiver is connected to an RJ45 port on the B126-004 using a single Cat5e/6 cable.

For longer extension distances, use a [B126-1A0](#) or [B126-1A0-WP-1](#) active receiver:

- A 1080p(60Hz) signal can be transmitted up to 150 ft.
- A 1080i(60Hz) signal can be transmitted up to 200 ft.
- A 3D signal can be transmitted up to 125 ft.

For shorter distances, use a [B126-1P0](#) passive receiver:

- A 1080p(60Hz) signal can be transmitted up to 50 ft.
- A 1080i(60Hz) signal can be transmitted up to 100 ft.

Highlights

- Ideal for HDMI digital signage applications requiring multiple displays
- Can extend an HDMI signal by hundreds of feet with the use of remote receiver units
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- HDCP and 3D compatible
- Compatible with both stereo audio and 7.1 channel surround sound audio (Multi-Channel or PCM)
- Supports 24-bit True Color (8-bits per channel)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B126-004 HDMI Over Cat5 Extender/Splitter, 4-Port
- 1 ft. HDMI daisychain cable
- Mounting hardware
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's Manual

- Cannot be used for a 3D signal

Further extend the signal range or add more displays by using a Tripp Lite [B126-110](#) Remote Repeater unit:

- Add up to three repeaters on each channel of the B126-004 for a total of 4 displays per channel(*A receiver should be the last unit in a channel*)
- A 1080p(60Hz) signal can be extended up to 125 ft. for each repeater added into a channel
- A 1080i(60Hz) signal can be extended up to 175 ft. for each repeater added into a channel
- A 3D signal can be extended up to 100 ft. for each repeater added into a channel

Features

Digital Signage Capabilities

- Connect up to 13 monitors(1 Local, 12 Remote) by daisy chaining up to three B126-004 transmitters.
- Connect up to 4 remote units in a repeater chain(3 repeaters and 1 active receiver) with a monitor at each location
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p(60Hz)
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, is required to achieve maximum distance and resolution
- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source and monitor
- Features an additional HDMI port for the connection of a local monitor, or to daisy chain additional units
- Compatible with both stereo audio and 7.1 channel surround sound audio(7.1 channel surround sound signal will be Multi-Channel or PCM)
- HDCP compatible
- Supports 24-bit True Color(8-bits per channel)

Distance and Extension Ranges

- Extends a 1080p(60Hz) signal up to 150 ft. when used with a [B126-1A0](#) or [B126-1A0-WP-1](#) active remote receiver unit
- Extends a 1080p(60Hz) signal up to 50 ft. when used with a [B126-1P0](#) passive remote receiver unit
- Extends a 3D signal up to 125 ft. when used with an active remote receiver unit. A 3D signal cannot be extended using a passive remote receiver unit
- Extends a 1080p(60Hz) signal up to 125 ft., or a 3D signal up to 100 ft., from the B126-004 transmitter to the first repeater unit
- Extends a 1080p(60Hz) signal up to an additional 125 ft., or a 3D signal up to an additional 100 ft., from each repeater unit to the next unit
- Further extend the signal range or add more displays by using a Tripp Lite [B126-110](#) Remote Repeater unit

Installation and Setup

- Plug and play; No drivers required
- Compatible with all HDMI video sources and all operating systems

Mounting Options

- The B126-004 includes mounting hardware enabling it to be installed in any venue
- Mounting options include wall-mount, rackmount and pole mount
- Mount up to 3 B126-004 transmitters in 1U of rack space using a Tripp Lite [B132-004-RB](#) rackmount bracket
- Mounting hardware included
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases

Specifications

OVERVIEW

Display Style

Splitter



Cable Type	HDMI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Optional Mounting Accessory Notes	Up to three B126-004 local units can be mounted in 1U of rack space using a Tripp Lite B132-004-RB Extender/Splitter 19in rackmount bracket
Unit Dimensions (hwd / in.)	1.125 x 5 x 4
Unit Dimensions (hwd / cm)	2.86 x 12.7 x 10.16
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	RJ45 (FEMALE) (X4)
Connector B	HDMI (FEMALE) (X2)
Ports	4
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>