

NetDirector 16-Port Cat5 IP KVM Switch 1U Rack-Mount 2+1 User

MODEL NUMBER: **B064-016-02-IPG**



Description

Tripp Lite's 16-port NetDirector Cat5 IP KVM Switch is the optimal solution for remotely controlling multiple computers (combination of PS/2, USB and Serial) by up to 3 (1 Local and 2 Remote) independent, simultaneous users. A full-screen graphical OSD with multi-level authentication (Super Administrator, Administrator and User) allows you to quickly and efficiently manage your installation, and can be displayed in English, German, Russian, Japanese, traditional Chinese and simplified Chinese. Critical events on the installation can be tracked via email notification, SNMP traps, the Windows based log server or Syslog server. Accessing the connected computers is a breeze; view multiple computers at the same time using panel array mode, automatically sync USB mice, access the on-screen keyboard feature in numerous language formats. Virtual Media allows computers connected using a [B055-001-USB-V2](#) Server Interface Unit to access DVD/CD drives, flash drives and other storage media as if they were directly connected to the computer. In addition, three USB ports are located on the front panel of the unit for use with Virtual Media or an external keyboard and mouse. Other features include dual power supplies that allow the unit to continue running in the event one power supply stops receiving power, temperature sensors that control the speed of the unit's cooling fans, remote authentication support via RADIUS, LDAP, LDAPS and Active Directory, dial-in modem access and non-browser access using Windows and Java applications. Constructed of heavy-duty steel housing.

Features

- Up to 3 users (1 Local, 2 Remote) can simultaneously access the connected computers/servers
- Features two RJ45 network ports for redundant or dual-IP operation
- Supports IPv4, Link Local IPv6 Address and IPv6 Stateless Auto configuration protocols
- Blade server support
- Multi-level authentication; Super Administrator, Administrator and User
- Advanced encryption technologies - 1024 bit RSA; 56 bit DES; 256 bit AES and 128 bit SSL
- View multiple ports at the same time using the panel array mode feature
- Virtual Media allows computers connected to the KVM using a [B055-001-USB-V2](#) SIU to access DVD/CD

Highlights

- Simultaneous support for 3 users (1 local, 2 remote)
- Supports IPv4, Link Local IPv6 Address and IPv6 Stateless Auto configuration protocols
- Blade server support
- Virtual Media allows computers connected using a [B055-001-USB-V2](#) SIU to access DVD/CD drives, flash drives and other storage media from a user's remote computer as if it were directly connected
- Remote Authentication: RADIUS, LDAP, LDAPS, and Active Directory
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Remote Console Computers (Web Browser) - To access the KVM switch via web browser, your computer needs to be running Sun's Java Runtime Environment (JRE) v.6, Update 3 or higher, and your browser must support 128-bit SSL encryption.
- Browsers - The NetDirector Cat5 IP KVM switch supports the following browsers; Internet Explorer, Firefox, Mozilla, Safari, Opera, Netscape and Google Chrome.
- Remote Console Computers (non-Browser Windows or Java Client) - To access the KVM switch using the non-browser based Windows client, your computer/server must be running Windows, and DirectX 7.0 or higher must be installed. To



- drives, flash drives and other storage media from a user's remote computer as if it were directly connected
- An additional three USB ports are located on the front of the KVM for the sharing of USB peripherals.
- Remote authentication support; RADIUS, LDAP, LDAPS and Active Directory
- Track critical events on the installation via email notification, SNMP traps, Windows-based Log Server or Syslog server
- Dual power supplies allow the unit to continue running in the event one power supply ceases to receive power
- Built-in sensors increase/decrease the speed of the unit's cooling fans according to the temperature
- Dial-in / Dial-out modem support
- Graphical OSD can be displayed in English, German, Russian, Japanese, traditional Chinese and simplified Chinese
- Supports up to 1600x1200 @ 60Hz resolutions
- Supports 10Base-T, 100Base-T, 1000Base-T, Auto-Sense, TCP/IP, HTTP, DNS, DHCP, UDP, ARP and Ping
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases
- Compatible with all major operating systems
- Constructed of heavy-duty steel housing

Specifications

OVERVIEW	
Users	3
Max CPU	16
PHYSICAL	
Unit Dimensions (hwd / in.)	1.75 x 17 x 16
Unit Dimensions (hwd / cm)	4.45 x 43.18 x 40.64
Unit Weight (lbs.)	17
Unit Weight (kg)	7.71
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	0 to 80% RH, Non-Condensing
Operating Temperature	0 to 50 C (32 to 122 F)
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	Yes

- access the non-browser based Java client, your computer must be running Sun's Java Runtime Environment (JRE) v.6, Update 3 or higher.
- Connected Computers/Servers - Computers/servers being connected to the KVM switch must have a VGA port and USB or PS/2 Keyboard and Mouse ports.
- Operating Systems - Compatible with all major operating systems

Package Includes

- B064-016-02-IPG (2+1 User) NetDirector Cat5 IP KVM switch
- (x2) C5 to 5-15P power cords
- CD with owner's manual, quick start guide and device files
- Quick start guide
- RJ45 to DB9 adapter for dial-In modem functionality
- USB/PS/2 combo console cable kit
- Grounding wire
- Set of foot pads
- Rackmount hardware



CONNECTIONS	
Ports	16
Computer/Server Ports	(x16) RJ45 Female
PC/Server Connections	VGA; USB; PS/2; Serial
Local Console Ports - Port 1	HD15 Female (via included console cable)
Local Console Ports - Port 2	(x2) USB Female (via included console cable)
Local Console Ports - Port 3	(x2) PS/2 Female (via included console cable)
SPECIAL FEATURES	
Cat5 KVM Switch	Yes
FEATURES & SPECIFICATIONS	
Autoscan (Y,N)	Y
Autoscan Duration	User-definable from 1 to 255 seconds; default of 5 seconds
CERTIFICATIONS	
Approvals	UL/cUL, FCC, CE, TAA, RoHS
NIAP-Certified Secure	No
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>