


STA-500 - Amplifier



Stereo PA amplifier, for general applications.

- Fan cooling
- 2 level controls
- Ground lift switch
- Speaker switch-on delay
- Protective circuit with LED indication for protection against short circuit, overheating and DC voltage overlay at the outputs
- 1 LED per channel for indicating overload (clip)

Technical Data

Output power	:
RMS power	:
4 Ohm	: 2 x 200 W _{RMS}
8 Ohm	: 2 x 125 W _{RMS}
Max. power	: 600 W _{MAX}
General information	:
Inputs	: 1.3 V/55 k Ohm
Frequency range	: 10-20,000 Hz
S/N ratio	: 64 dB
Crosstalk attenuation	: ? 55 dB
THD	: < 0.05 %
Power supply	: 230 V~/50 Hz/730 VA
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 482x95x300 mm, 2 RS
Weight	: 7.6 kg
Inputs	: 1 x 6.3 mm jack L/R, : 1 x RCA L/R
Outputs	: 2 x SPEAKER : 1 x 6.3 mm jack L/R : 2 x pair of screw terminals