

## NetDirector 16-Port 1U Rack-Mount Console KVM Switch w/17-in. LCD and IP Remote Access

MODEL NUMBER: **B020-016-17-IP**



### Description

The B020-016-17-IP Console KVM Switch with built-in IP access allows secure access to multiple computers from a single keyboard, monitor and mouse. It consists of an integrated 16-Port IP KVM switch, 17" LCD monitor, keyboard and touchpad, all in a 1U rackmountable housing. A single B020-016-17-IP can control up to 16 directly connected computers.

The LCD and keyboard/touch pad modules slide independently of each other. To maximize space, the keyboard/touch pad module slides back to "hide away" when not in use, while the thin profile LCD monitor rotates back flush against the rack allowing convenient monitoring of computer activity.

The B020-016-17-IP features IP-based connectivity that allows one local operator and one remote operator to simultaneously monitor and access the computers attached to the console. Because it uses TCP/IP for its communications protocol, the B020-016-17-IP can be accessed from any computer on the LAN, WAN or Internet whether that computer is located down the hall, down the street or halfway around the world. For Government purchasers, B020-016-17-IP is Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. Compatible with all major operating systems. Constructed of heavy-duty steel housing.

### Features

- Control up to 16 directly connected computers
- Remotely access computers via the LAN, WAN or Internet
- Remotely access the KVM via browser or non-browser applications
- Both IPv4 and IPv6 are supported
- Network interfaces - TCP/IP, HTTP, HTTPS, UDP, RADIUS, DHCP, SSL, ARP, DNS, 10Base-T/100Base-TX, Auto Sense, and Ping
- Advanced encryption technologies include 1024-bit RSA, 256-bit AES, 56-bit DES, 128-bit SSL
- Supports RADIUS server authentication
- Panel array mode - Monitor multiple ports at the same time
- Dual-Rail - Slide the keyboard module into the rack while the monitor remains open for viewing.
- Dual-Bus - Supports simultaneous access for 1 local and 1 remote user
- Includes a Windows-based log server, providing a more robust method of tracking events on the installation

### Highlights

- 16-Port console KVM switch with built-in IP access
- Both IPv4 and IPv6 are supported
- Dual-Rail - Push keyboard in while the LCD monitor remains open
- Multi-level password security
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Compatible with all major operating systems

### Package Includes

- B020-016-17-IP Console KVM Switch with built-in IP access
- PS/2 KVM Cable Kit
- USB KVM Cable Kit
- C13 to 5-15P power cord
- CD with owner's manual



- Built-in monitor supports video resolutions up to 1280 x 1024 @ 75Hz; resolutions up to 1600 x 1200 @ 60Hz are supported when accessing the KVM from a remote computer
- Power Consumption: 120V, 60Hz, 31W; 230V, 50Hz, 39W
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Compatible with all major operating systems
- Constructed of heavy-duty steel housing

## Specifications

OVERVIEW	
Users	1
Console	Yes
Max CPU	16
INPUT	
Recommended Electrical Service	100-250V
Maximum Input Amps	1
PHYSICAL	
Unit Dimensions (hwd / in.)	1.75 x 19 x 27.8
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 70.61
Unit Weight (lbs.)	38.1
Unit Weight (kg)	17.28
Color	Black
LCD Monitor (in.)	17
LCD Monitor (cm)	43.18
ENVIRONMENTAL	
Storage Temperature Range	-20 to +60 degrees C
Relative Humidity	0% to 80% RH, Non-condensing
Operating Temperature	0 to 40 degrees C
BTUs	100.7 to 102.42
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	Yes
CONNECTIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Ports	16
Computer/Server Ports	(x16) HD15 Female
Other Ports	RJ45 Female
PC/Server Connections	PS/2
Local Console Ports - Port 1	HD15 Female
Local Console Ports - Port 2	(x3) MiniDIN6 Female
<b>SPECIAL FEATURES</b>	
Cat5 KVM Switch	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
Autoscan (Y,N)	Y
Autoscan Duration	1 - 255 Seconds
<b>CERTIFICATIONS</b>	
Certifications	UL 60950-1 (USA), CAN/CSA (Canada), FCC Part 15 Class A, CE
NIAP-Certified Secure	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>