

BMP®71 Label Printer

www.BradyID.com/bmp71

Portable Label Printers



Online Video!

Visit www.BradyID.com/bmp71 or scan this code for more information or to view an online printer demo video.

Your Complete Printing Solution:

BMP®71 Material RollsPage 70
 BMP®71 Print RibbonsPage 80

Part Number	Description
BMP71	BMP71 Printer*
BMP71-LM	BMP71 Printer* w/ LabelMark Standard Software
BMP71-MW	BMP71 Printer* w/ Markware Lean Software
BMP71-QC	BMP71 Printer* w/ Quick Charger
BMP71-SC	BMP71 Printer* w/ Soft Case
BMP71-SC-QC	BMP71 Printer* w/ Soft Case and Quick Charger
M71-AC-BC	BMP71 AC/Battery Adaptor
M71-ADAPT	TLS/Handimark Media Adaptor
M71-BATT	BMP71 Battery Pack
M71-CABLE	BMP71 USB Cable
M71-CLEAN	BMP71 Cleaning Kit
M71-HC	BMP71 Hardcase
M71-QC	BMP71 Quick Charger
M71-SC	BMP71 Softcase
BMP71-360	Brady360® Replacement Plan
BMP71-360-KIT	BMP71 Printer* w/ Brady360® Replacement Program

*Printer ships with Hardcase, Charger/AC Adapter, (1) Roll of M71-31-423 White Die Cut Labels, (1) M71-R6000 Black Ribbon Cartridge, Media Adapter, Rechargeable Battery, USB Cable, Quickstart Guide, drivers CD, Users Guide, Tutorial and 1 year Limited Warranty.
 U.S. Patent No. 7,999,836; 8,328,442; 8,333,524.

BMP®71 LABEL PRINTER

Thousands Of Applications. Hundreds Of Labels. One Label Printer.

The most versatile portable printer in our offering. Painless setup, robust label offering and intuitive interface come together in our top-of-the-line portable printer.

Text and Print Options:

- 100's Of Symbols
- Reverse Print
- Subscripts
- Auto Font Size
- Barcodes
- Time/Date Stamps
- Underline/Italics/Bold
- Serialization
- Vertical Printing
- And more!



Did You Know?

The BMP71 printer can also print on TLS2200® and HandiMark® consumables using the included media adaptor!

BMP71 Label Printer Specifications	
Max Labels Per Day	1000 labels/day
Print Resolution	300 dpi
Print Technology	Thermal Transfer
Print Speed	38 mm/sec (1.50 in/sec)
Tape Widths (in)	Various sizes from 0.25" to 2.00"
Tape Widths (mm)	Various sizes from 6.4 to 50.8 mm
Max Label Width	2.00"
Max Print Width	1.75"
Memory	200 MB
Materials Supported	Continuous, Die Cut labels, Bulk, over 400 Stock Parts and Custom
Continuous vs Die Cut Labels	Continuous and die cut labels
PC Connectivity	Yes
Software Compatibility	LabelMark™ / MarkWare™ Software
Data Transfer from PC to printer	Yes
Wireless Connectivity	No
Stand Alone Printing	Yes
Connectivity Options	USB
Color Capability	Single Color Printing
Keyboard	QWERTY
Backlit Screen	Yes
Text Sizes	4 to 174 point + autosizing
Multi-Line Print	Yes
Print Rotation	Yes
Serialization	Yes - multiple and linked
Barcode	39 and 128
Symbols	Over 500
Portability	Yes
Label Types or Application Functions	Banner Portrait, Banner Landscape, Wire, Flag Labels, Patch Panel, Terminal Block, Desi Strip, 110 Block, 66 Block, Bix Block, Fixed Length, Pipe Markers, Safety Labels
Applications	Circuit Board Labeling, Data Communications Labeling, Facility, Safety & Maintenance Identification, General & Industrial Labeling, Panel Identification, Security Identification, Wire & Cable Marking, Pipe Marking
Power Supply	Rechargeable Battery, AC Power
Weight	5.49 lbs (2.49kg)
Warranty	12 months - See Terms and Conditions



Brady 360® Replacement Printer Plan

supplements the Limited Warranty already included with your printer purchase. This Replacement Plan allows you can return your qualified printer for a replacement printer within the first 12 months of purchase. You must purchase the replacement program at the time of printer purchase in order to receive benefits.

*Printheads are covered. *Limit of two printers in the first 12 months of initial purchase.

The one way to faster, easier label printing.



Electrical Labeling



Voice & Data Communications



General Identification



PermaSleeve® Wire Marking Sleeves



Self-Laminating Labels



Safety Labels ...and many more!