

Capacitor, ceramic, 10 pF, +/-5% Tol, 50 V, COG, Lead Spacing=0.2"



General Information	
Supplier:	KEMET
Application:	General Purpose
Temperature Coefficient:	COG
Body Type:	Radial Conformal
Lead Type:	Wire Leads
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications	
Capacitance:	10 pF
Voltage:	50 V
Tolerance:	+/-5%
Temperature Range:	-55/+125C
Failure Rate:	NA
Dissipation Factor:	0.1%
Insulation Resistance:	100 GOhm
Dielectric Strength:	125 V

Dimensions (in)		
Symbol	Dimension	Tolerance
L	0.15	MAX
H	0.2	MAX
T	0.1	MAX
S	0.2	NOM
LL	0.276	MIN
F	0.02	NOM

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500