

DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Version	Revision Date:	SDS Number:	Date of last issue: 08/20/2015
1.3	09/30/2015	1312923-00004	Date of first issue: 02/12/2015

SECTION 1. IDENTIFICATION

Product name : DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Product code : 000000000001892011

Manufacturer or supplier's details

Company name of supplier : Dow Corning Corporation

Address : South Saginaw Road
Midland Michigan 48686

Telephone : (989) 496-6000

Emergency telephone : 24 Hour Emergency Telephone : (989) 496-5900
CHEMTREC : (800) 424-9300

Recommended use of the chemical and restrictions on use

Recommended use : Adhesive, binding agents

SECTION 2. HAZARDS IDENTIFICATION

GHS Classification

Not a hazardous substance or mixture.

GHS Label element

Not a hazardous substance or mixture.

Precautionary Statements : **Prevention:**
P271 Use only outdoors or in a well-ventilated area.

Other hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Chemical nature : Silicone elastomer

Hazardous ingredients

Chemical name	CAS-No.	Concentration (% w/w)
Silicon dioxide	7631-86-9	>= 5 - < 10
Carbon black	1333-86-4	>= 0.1 - < 1

SECTION 4. FIRST AID MEASURES

DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Version 1.3	Revision Date: 09/30/2015	SDS Number: 1312923-00004	Date of last issue: 08/20/2015 Date of first issue: 02/12/2015
----------------	------------------------------	------------------------------	---

If inhaled	: If inhaled, remove to fresh air. Get medical attention if symptoms occur.
In case of skin contact	: Wash with water and soap as a precaution. Get medical attention if symptoms occur.
In case of eye contact	: Flush eyes with water as a precaution. Get medical attention if irritation develops and persists.
If swallowed	: If swallowed, DO NOT induce vomiting. Get medical attention if symptoms occur. Rinse mouth thoroughly with water.
Most important symptoms and effects, both acute and delayed	: None known.
Protection of first-aiders	: No special precautions are necessary for first aid responders.
Notes to physician	: Treat symptomatically and supportively.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable extinguishing media	: Water spray Alcohol-resistant foam Carbon dioxide (CO ₂) Dry chemical
Unsuitable extinguishing media	: None known.
Specific hazards during fire fighting	: Exposure to combustion products may be a hazard to health.
Hazardous combustion products	: Carbon oxides Silicon oxides Formaldehyde
Specific extinguishing methods	: Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Use water spray to cool unopened containers. Remove undamaged containers from fire area if it is safe to do so. Evacuate area.
Special protective equipment for fire-fighters	: Wear self-contained breathing apparatus for firefighting if necessary. Use personal protective equipment.

SECTION 6. ACCIDENTAL RELEASE MEASURES

DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Version 1.3	Revision Date: 09/30/2015	SDS Number: 1312923-00004	Date of last issue: 08/20/2015 Date of first issue: 02/12/2015
----------------	------------------------------	------------------------------	---

- Personal precautions, protective equipment and emergency procedures : Follow safe handling advice and personal protective equipment recommendations.
- Environmental precautions : Discharge into the environment must be avoided. Prevent further leakage or spillage if safe to do so. Retain and dispose of contaminated wash water. Local authorities should be advised if significant spillages cannot be contained.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material. For large spills, provide diking or other appropriate containment to keep material from spreading. If diked material can be pumped, store recovered material in appropriate container. Clean up remaining materials from spill with suitable absorbent. Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable. Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

SECTION 7. HANDLING AND STORAGE

- Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
- Local/Total ventilation : Use only with adequate ventilation.
- Advice on safe handling : Handle in accordance with good industrial hygiene and safety practice. Take care to prevent spills, waste and minimize release to the environment.
- Conditions for safe storage : Keep in properly labeled containers. Store in accordance with the particular national regulations.
- Materials to avoid : Do not store with the following product types:
Strong oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Ingredients with workplace control parameters

Ingredients	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Silicon dioxide	7631-86-9	TWA (Dust)	20 Million particles per cubic foot (Silica)	OSHA Z-3

DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Version 1.3 Revision Date: 09/30/2015 SDS Number: 1312923-00004 Date of last issue: 08/20/2015
 Date of first issue: 02/12/2015

		TWA (Dust)	80 mg/m ³ / %SiO ₂ (Silica)	OSHA Z-3
		TWA	6 mg/m ³ (Silica)	NIOSH REL
Carbon black	1333-86-4	TWA	3.5 mg/m ³	NIOSH REL
		TWA	3.5 mg/m ³	OSHA Z-1
		TWA (Inhalable fraction)	3 mg/m ³	ACGIH

Engineering measures : Processing may form hazardous compounds (see section 10).
 Ensure adequate ventilation, especially in confined areas.
 Minimize workplace exposure concentrations.

Personal protective equipment

Respiratory protection : No personal respiratory protective equipment normally required.

Hand protection

Remarks : Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
 Safety glasses

Skin and body protection : Skin should be washed after contact.

Hygiene measures : Ensure that eye flushing systems and safety showers are located close to the working place.
 When using do not eat, drink or smoke.
 Wash contaminated clothing before re-use.
 These precautions are for room temperature handling. Use at elevated temperature or aerosol/spray applications may require added precautions.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : paste

Color : black

Odor : Acetic acid

Odor Threshold : No data available

pH : Not applicable

Melting point/freezing point : No data available

Initial boiling point and boiling range : Not applicable

**DOW CORNING(R) 732 MULTI-PURPOSE
SEALANT, BLACK**

Version	Revision Date:	SDS Number:	Date of last issue: 08/20/2015
1.3	09/30/2015	1312923-00004	Date of first issue: 02/12/2015

Flash point	:	Not applicable
Evaporation rate	:	Not applicable
Flammability (solid, gas)	:	Not classified as a flammability hazard
Upper explosion limit	:	No data available
Lower explosion limit	:	No data available
Vapor pressure	:	Not applicable
Relative vapor density	:	No data available
Relative density	:	1.04
Solubility(ies)	:	
Water solubility	:	No data available
Partition coefficient: n-octanol/water	:	No data available
Autoignition temperature	:	No data available
Decomposition temperature	:	No data available
Viscosity	:	
Viscosity, dynamic	:	Not applicable
Explosive properties	:	Not explosive
Oxidizing properties	:	The substance or mixture is not classified as oxidizing.
Molecular weight	:	No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity	:	Not classified as a reactivity hazard.
Chemical stability	:	Stable under normal conditions.
Possibility of hazardous reactions	:	Use at elevated temperatures may form highly hazardous compounds. Can react with strong oxidizing agents. Acetic acid is formed upon contact with water or humid air. Hazardous decomposition products will be formed at elevated temperatures.
Conditions to avoid	:	None known.
Incompatible materials	:	Oxidizing agents

**DOW CORNING(R) 732 MULTI-PURPOSE
SEALANT, BLACK**

Version	Revision Date:	SDS Number:	Date of last issue: 08/20/2015
1.3	09/30/2015	1312923-00004	Date of first issue: 02/12/2015

Hazardous decomposition products
Thermal decomposition : Formaldehyde

SECTION 11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure**

Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Ingredients:**Silicon dioxide:**

Acute oral toxicity : LD50 (Rat): > 3,300 mg/kg
Assessment: The substance or mixture has no acute oral toxicity
Remarks: Information taken from reference works and the literature.

Acute inhalation toxicity : LC50 (Rat): > 2.08 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist
Assessment: The substance or mixture has no acute inhalation toxicity
Remarks: Information taken from reference works and the literature.

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: Information taken from reference works and the literature.

Carbon black:

Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg
Acute inhalation toxicity : LC50 (Rat): > 0.0046 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist

Skin corrosion/irritation

Not classified based on available information.

Product:

Result: No skin irritation
Remarks: Based on data from similar materials

Ingredients:**Silicon dioxide:**

**DOW CORNING(R) 732 MULTI-PURPOSE
SEALANT, BLACK**

Version	Revision Date:	SDS Number:	Date of last issue: 08/20/2015
1.3	09/30/2015	1312923-00004	Date of first issue: 02/12/2015

Result: No skin irritation
Remarks: Information taken from reference works and the literature.

Carbon black:
Species: Rabbit
Result: No skin irritation

Serious eye damage/eye irritation
Not classified based on available information.

Product:
Result: No eye irritation
Remarks: Based on data from similar materials

Ingredients:
Silicon dioxide:
Result: No eye irritation
Remarks: Information taken from reference works and the literature.

Carbon black:
Species: Rabbit
Result: No eye irritation

Respiratory or skin sensitization
Skin sensitization: Not classified based on available information.
Respiratory sensitization: Not classified based on available information.

Ingredients:
Silicon dioxide:
Assessment: Does not cause skin sensitization.

Test Type: Skin: test type not specified
Species: Guinea pig
Remarks: Information taken from reference works and the literature.

Carbon black:
Test Type: Buehler Test
Routes of exposure: Skin contact
Species: Guinea pig
Method: OECD Test Guideline 406
Result: negative

Germ cell mutagenicity
Not classified based on available information.

Ingredients:
Silicon dioxide:
Genotoxicity in vitro : Result: negative
Remarks: Information taken from reference works and the literature.

DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Version	Revision Date:	SDS Number:	Date of last issue: 08/20/2015
1.3	09/30/2015	1312923-00004	Date of first issue: 02/12/2015

Genotoxicity in vivo : Application Route: Ingestion
Result: negative
Remarks: Information taken from reference works and the literature.

Germ cell mutagenicity - Assessment : Animal testing did not show any mutagenic effects.

Carbon black:
Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Carcinogenicity

Not classified based on available information.

IARC Group 2B: Possibly carcinogenic to humans

Carbon black 1333-86-4

OSHA

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Reproductive toxicity

Not classified based on available information.

STOT-single exposure

Not classified based on available information.

STOT-repeated exposure

Not classified based on available information.

Ingredients:

Carbon black:

Routes of exposure: inhalation (dust/mist/fume)

Assessment: No significant health effects observed in animals at concentrations of 0.2 mg/l/6h/d or less.

Repeated dose toxicity

Ingredients:

Carbon black:

Species: Rat

NOAEL: 1 mg/m³

LOAEL: 7 mg/m³

Application Route: Inhalation

Test atmosphere: dust/mist

Exposure time: 90 d

Remarks: The substance is inextricably bound in the product and therefore does not contribute

DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Version 1.3	Revision Date: 09/30/2015	SDS Number: 1312923-00004	Date of last issue: 08/20/2015 Date of first issue: 02/12/2015
----------------	------------------------------	------------------------------	---

to a dust inhalation hazard.

Aspiration toxicity

Not classified based on available information.

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

Ingredients:

Carbon black:

- | | |
|---|---|
| Toxicity to fish | : LC0 (Danio rerio (zebra fish)): 1,000 mg/l
Exposure time: 96 h
Method: OECD Test Guideline 203 |
| Toxicity to daphnia and other aquatic invertebrates | : EC50 (Daphnia magna (Water flea)): > 5,600 mg/l
Exposure time: 24 h
Method: OECD Test Guideline 202 |
| Toxicity to algae | : NOEC (Desmodesmus subspicatus (green algae)): 10,000 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201 |

Persistence and degradability

No data available

Bioaccumulative potential

No data available

Mobility in soil

No data available

Other adverse effects

No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

- | | |
|---|---|
| Resource Conservation and Recovery Act (RCRA) | : This product has been evaluated for RCRA characteristics and does not meet the criteria of hazardous waste if discarded in its purchased form. |
| Waste from residues | : Dispose of in accordance with local regulations. |
| Contaminated packaging | : Empty containers should be taken to an approved waste handling site for recycling or disposal.
If not otherwise specified: Dispose of as unused product. |

DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Version	Revision Date:	SDS Number:	Date of last issue: 08/20/2015
1.3	09/30/2015	1312923-00004	Date of first issue: 02/12/2015

SECTION 14. TRANSPORT INFORMATION

International Regulation

UNRTDG

Not regulated as a dangerous good

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

Domestic regulation

49 CFR

Not regulated as a dangerous good

SECTION 15. REGULATORY INFORMATION

EPCRA - Emergency Planning and Community Right-to-Know

CERCLA Reportable Quantity

Ingredients	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
Acetic acid	64-19-7	5000	*
Acetic anhydride	108-24-7	5000	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : No SARA Hazards

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

US State Regulations

Pennsylvania Right To Know

Dimethyl siloxane, hydroxy-terminated	70131-67-8	70 - 90 %
Silicon dioxide	7631-86-9	5 - 10 %
Distillates (petroleum), hydrotreated middle	64742-46-7	0.1 - 1 %

DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Version	Revision Date:	SDS Number:	Date of last issue: 08/20/2015
1.3	09/30/2015	1312923-00004	Date of first issue: 02/12/2015

Acetic acid	64-19-7	0 - 0.1 %
Acetic anhydride	108-24-7	0 - 0.1 %

New Jersey Right To Know

Dimethyl siloxane, hydroxy-terminated	70131-67-8	70 - 90 %
Silicon dioxide	7631-86-9	5 - 10 %
Dimethyl siloxane, trimethylsiloxy-terminated	63148-62-9	1 - 5 %
Carbon black	1333-86-4	0.1 - 1 %

California Prop. 65

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

The ingredients of this product are reported in the following inventories:

NZIoC	: All ingredients listed or exempt.
REACH	: All ingredients (pre-)registered or exempt.
TSCA	: All chemical substances in this material are included on or exempted from listing on the TSCA Inventory of Chemical Substances.
AICS	: All ingredients listed or exempt.
IECSC	: All ingredients listed or exempt.
KECI	: All ingredients listed, exempt or notified.
DSL	: All chemical substances in this product comply with the CEPA 1999 and NSNR and are on or exempt from listing on the Canadian Domestic Substances List (DSL).


DOW CORNING(R) 732 MULTI-PURPOSE SEALANT, BLACK

Version 1.3 Revision Date: 09/30/2015 SDS Number: 1312923-00004 Date of last issue: 08/20/2015
 Date of first issue: 02/12/2015

SECTION 16. OTHER INFORMATION

Further information

NFPA:



HMIS III:

HEALTH	0
FLAMMABILITY	1
PHYSICAL HAZARD	0

0 = not significant, 1 = Slight,
 2 = Moderate, 3 = High
 4 = Extreme, * = Chronic

Full text of other abbreviations

ACGIH : USA. ACGIH Threshold Limit Values (TLV)
 NIOSH REL : USA. NIOSH Recommended Exposure Limits
 OSHA Z-1 : USA. Occupational Exposure Limits (OSHA) - Table Z-1 Limits for Air Contaminants
 OSHA Z-3 : USA. Occupational Exposure Limits (OSHA) - Table Z-3 Mineral Dusts
 ACGIH / TWA : 8-hour, time-weighted average
 NIOSH REL / TWA : Time-weighted average concentration for up to a 10-hour workday during a 40-hour workweek
 OSHA Z-1 / TWA : 8-hour time weighted average
 OSHA Z-3 / TWA : 8-hour time weighted average

AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CERCLA - Comprehensive Environmental Response, Compensation, and Liability Act; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DOT - Department of Transportation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; EHS - Extremely Hazardous Substance; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; HMIS - Hazardous Materials Identification System; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; MSHA - Mine Safety and Health Administration; n.o.s. - Not Otherwise Specified; NFPA - National Fire Protection Association; NO(A)EC - No Ob-

**DOW CORNING(R) 732 MULTI-PURPOSE
SEALANT, BLACK**

Version	Revision Date:	SDS Number:	Date of last issue: 08/20/2015
1.3	09/30/2015	1312923-00004	Date of first issue: 02/12/2015

served (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; RCRA - Resource Conservation and Recovery Act; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RQ - Reportable Quantity; SADT - Self-Accelerating Decomposition Temperature; SARA - Superfund Amendments and Reauthorization Act; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative

Sources of key data used to compile the Material Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Revision Date : 09/30/2015

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

US / Z8