


ITT Cannon offers the largest variety of locking and latching hardware.


Product Features

- Ensures positive mating
- Provides locking and latching for high vibration applications

Front Panel Mount



Rear Panel Mount




Female Screw Lock


- Kit consists of 1 nut, 3 washers, 1 lock washer, 1 hex nut
- Order 2 per connector



Front Panel Mount



Rear Panel Mount



Note:
(1) A 6 inch/pound (female) and 4 inch/pound (male) maximum torque during assembly is recommended on steel screw lock assemblies.
(2) A third flat washer is supplied for panel mounting of tab shell connectors.


100 µin Au	50 µin Au	Stainless Steel	A ±0,38 (.015)
D20418-52	D20418-139	D20418-14	7,92 (.312)
D20418-73	D20418-141	D20418-102	12,70 (.500)
D20418-126	D20418-142	D20418-77	15,88 (.625)

Male Screw Lock

- Kit consists of 1 screw and 1 clip
- Order 2 per connector

Materials and Finishes

Material:	Copper Alloy
Finish:	Gold over Copper



100 µin Au	50 µin Au*	Stainless Steel	A ±0,38 (.015)	B ±0,25 (.010)	C ±0,13 (.005)	For Shell Size
D20419-74	D20419-223	D20419-14	14,10 (.555)	6,35 (.250)	1,22 (.048)	DE,DA,DB,DC
D20419-48	-	D20419-28	14,10 (.555)	7,14 (.281)	1,22 (.048)	DE,DA,DB,DC
D20419-73	D20419-225	D20419-38	14,10 (.555)	7,14 (.281)	1,70 (.067)	DE,DA,DB,DC
D20419-84	D20419-224	-	14,10 (.555)	7,14 (.281)	2,34 (.092)	DE,DA,DB,DC
D20420-67	D20420-171	D20420-21	16,66 (.656)	6,35 (.250)	1,22 (.048)	DD
D20420-49	D20420-170	D20420-136	16,66 (.656)	7,14 (.281)	1,70 (.067)	DD
D20420-63	D20420-172	D20420-70	16,66 (.656)	7,14 (.281)	2,34 (.092)	DD
D20420-88	-	-	16,66 (.656)	7,92 (.312)	2,34 (.092)	DD

* Kit consists of two screws and two clips

Dimensions shown in mm

Specifications and dimensions subject to change

www.ittcannon.com