


S-8 SINGLE CONTACT BAYONET BASE

MINIATURE LAMP

28V .900A

WAMCO PART NO.	ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE			
WL-315	S-8	BA15s	28V .900A	C-2V			
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS
28V	MIN	NOM	MAX	MIN	NOM	MAX	300
	.810	.900	.990	24.0	32.0	40.0	

DIMENSIONAL CHARACTERISTICS



NOTES

1. LCL = 1.13" (28.7mm)
2. Nickel-plated brass construction base
3. Part mark WL-315
4. RoHS compliant
5. ANSI trade number 315

