


## Background Music Loudspeakers

Indoor background music loudspeakers featuring ABS enclosures and sturdy metal grilles. Suitable for free standing or wall mounting via adjustable pivot fixing bracket, allowing horizontal or vertical installation. The trapezoidal design allows for the enclosures to be mounted neatly into corners, making them ideal for installation into bars, cafés, hotels and offices.


- 2-way 100V line loudspeakers
- Complete with adjustable mounting brackets
- Supplied in pairs
- Multiple power taps plus low impedance
- Available in black or white
- Robust housing
- Polypropylene LF
- Mylar HF (BGS 50T)
- Soft dome HF (BGS 85T)



### BGS 50T



### BGS 85T



**100V**  
line

**x2**  
SUPPLIED  
IN PAIRS

$\Omega$   
LOW  
IMPEDANCE

**50W**  
rms

**100V**  
line

**x2**  
SUPPLIED  
IN PAIRS

$\Omega$   
LOW  
IMPEDANCE

**85W**  
rms

Specifications	BGS 50T	BGS 85T
Input:	100V, 8 $\Omega$	100V, 8 $\Omega$
Power taps @ 100V:	4W, 8W, 16W, 30W	4W, 8W, 16W, 30W
Impedance:	2.5K $\Omega$ , 1.25K $\Omega$ , 625 $\Omega$ , 333 $\Omega$	2.5K $\Omega$ , 1.25K $\Omega$ , 625 $\Omega$ , 333 $\Omega$
Power (RMS):	50W @ 8 $\Omega$	85W @ 8 $\Omega$
Sensitivity (1W/1m):	89dB	90dB
Maximum SPL (Rated W/1m):	103dB	105dB
Frequency response:	55Hz-20kHz	45Hz-20kHz
Drivers:	6.5" LF, 1" HF	8" LF, 1" HF
Connections:	2 x binding terminals	2 x binding terminals
Dimensions:	290 x 215 x 190mm	360 x 270 x 255mm
Weight:	3.8kg (each)	6.4kg (each)
Order code:	CRSP47 (white), CRSP48 (black)	CRSP49 (white), CRSP50 (black)

**Weather  
Resistant  
IP66 Horn  
Loudspeakers  
are available**

see pages 17-18

