



Description

- 2.4mm PVC insulation
- Conductor is high strength 7-strand tinsel wire for strength and durability
- Low-profile conical head helps prevent cord from being knocked off
- Built-in 10mm socket fits stud on mat
- 1 megohm (1×10^6 ohms) current limiting resistor in conical head end
- Ground cord wire terminated with M5 ring terminal
- Made in Taiwan

“EPA ground cords shall be used to make electrical connections between groundable points and the EPA ground facility.

Where a single resistor is used in the EPA ground cord, this shall be located near the groundable point. Where more than one resistor is used, a resistor of a minimum resistance value of one half the total resistance shall be located near the groundable point.

When accessible, the EPA ground cord and its groundable point connection shall be shrouded by insulating material.” (EN 61340-5-1 section 5.3.4 EPA ground cords)

Item #	Description
VER-26986	CORD,EBP,CONICAL,4.5M,10MMSKT, M5 RT,1 MEG

*Unless otherwise noted, tolerance $\pm 10\%$
Specifications and procedures subject to change without notice.*

Vermason

Straight Cords with Conical Head, 10mm Socket

VERMASON
UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH,
HERTS, SG6 2TD UK
PHONE: +44 (0) 1462-672005
E-MAIL: Service@Vermason.co.uk, INTERNET: Vermason.co.uk

Drawing Number
VER-26986

DATE:
September
2015