

Accessories



Locking device for cable to cable connection, snaps on to female and male connectors, GST 18i 3/4 or 5 pole

(VDE 0628 requires the use of a locking device)




Locking device for solder components GST 18i 3/4 or 5 pole, snaps on to female or male connectors

(VDE 0628 requires the use of a locking device)




Cover for female connectors¹⁾ GST 18i 3/4/5/6 pole

12 pole pack for covering open contacts



Snap-on locking slide¹⁾ GST 18i 3/4/5 pole

(VDE 0628 requires the use of a locking device)




Color	Part No.	Std. Pack	Part No.	Std. Pack	Part No.	Std. Pack	Part No.	Std. Pack
black	05.587.3156.1	50	05.590.4556.1	50	05.564.5353.0		05.595.1453.0	100
white	05.587.3156.0	50	05.590.4556.0	50			05.595.1453.2	100

Locking devices required

Combinations of locking devices	Incoming supply EIB V	Incoming supply EIB M	GST/EST connector (only snap-in and distribution blocks)	Solder components
Flat cable adapter GST/EST mains, 3 pole	-	-	05.587.3156.1 05.587.3156.0	05.590.4556.1 05.590.4556.0
Flat cable adapter GST/EST mains, 5 pole	05.590.4556.1 05.590.4556.0	05.590.4556.1 05.590.4556.0	05.587.3156.1 05.587.3156.0	05.590.4556.1 05.590.4556.1
GST/EST connector (only snap-in and distribution blocks)	05.587.3156.1 05.587.3156.0	05.587.3156.1 05.587.3156.0	05.587.3156.1 05.587.3156.0	05.590.4556.1 05.590.4556.2





Locking slide for distribution units¹⁾ GST 18i 3/5 pole


(VDE 0628 requires the use of a locking device)



²⁾ Note: Catalog products are standardly equipped with locking devices.

05.588.5753.1	50
05.588.5753.0	50

Cover for female connectors GST18i 3 pole for covering open contacts	Ferrules for GST 18 connectors with insulating sleeve for 0.5 through 1.5 mm ² conductors, according to DIN 46 228 T4	Ferrules for spring-loaded RST 20i3 connectors with insulating sleeve for conductors of 0.5 mm ² (DIN 46228-E0.5-10) 0.75 mm ² (DIN 46228-E0.75-12) 1.0 mm ² (DIN 46228-E1.0-12) 1.5 mm ² (DIN 46228-E1.5-12)	Screwdriver according to DIN 5264																																
	<p>Materials: Sleeve: Polypropylene, temperature resistance 105 °C, resistant to creepage</p> <p>Tubes: E-Cu, galvanized tin-plating</p> 	<p>Materials: Sleeve: Polypropylene, temperature resistance 105 °C, resistant to creepage</p> <p>Tubes: E-Cu, galvanized tin-plating</p> 																																	
<table border="1"> <thead> <tr> <th>Part No.</th> <th>Std. Pack</th> </tr> </thead> <tbody> <tr> <td>05.561.3653.1</td> <td>100</td> </tr> <tr> <td>05.561.3653.0</td> <td>100</td> </tr> </tbody> </table>	Part No.	Std. Pack	05.561.3653.1	100	05.561.3653.0	100	<table border="1"> <thead> <tr> <th>Part No.</th> <th>Std. Pack</th> </tr> </thead> <tbody> <tr> <td>0.5 mm² 06.600.2027.0 white</td> <td></td> </tr> <tr> <td>0.75 mm² 06.600.2127.0 gray</td> <td></td> </tr> <tr> <td>1.00 mm² 06.600.2227.0 red</td> <td></td> </tr> <tr> <td>1.50 mm² 06.600.2327.0 black</td> <td></td> </tr> </tbody> </table>	Part No.	Std. Pack	0.5 mm² 06.600.2027.0 white		0.75 mm² 06.600.2127.0 gray		1.00 mm² 06.600.2227.0 red		1.50 mm² 06.600.2327.0 black		<table border="1"> <thead> <tr> <th>Part No.</th> <th>Std. Pack</th> </tr> </thead> <tbody> <tr> <td>0.5 mm² 06.600.3827.0 white</td> <td></td> </tr> <tr> <td>0.75 mm² 06.600.3727.0 gray</td> <td></td> </tr> <tr> <td>1.00 mm² 06.600.3627.0 red</td> <td></td> </tr> <tr> <td>1.50 mm² 06.600.3927.0 black</td> <td></td> </tr> </tbody> </table>	Part No.	Std. Pack	0.5 mm² 06.600.3827.0 white		0.75 mm² 06.600.3727.0 gray		1.00 mm² 06.600.3627.0 red		1.50 mm² 06.600.3927.0 black		<table border="1"> <thead> <tr> <th>Part No.</th> <th>Std. Pack</th> </tr> </thead> <tbody> <tr> <td>06.502.4000.0</td> <td></td> </tr> <tr> <td>06.502.4300.0</td> <td></td> </tr> </tbody> </table> <p>For opening the clamping body of spring contacts in the GST 18 connector system and DIN rail terminal blocks Blade: 0.6 x 3.5 mm</p> <p>For spring-loaded RST connections Blade: 0.4 x 2.5 mm</p>	Part No.	Std. Pack	06.502.4000.0		06.502.4300.0	
Part No.	Std. Pack																																		
05.561.3653.1	100																																		
05.561.3653.0	100																																		
Part No.	Std. Pack																																		
0.5 mm² 06.600.2027.0 white																																			
0.75 mm² 06.600.2127.0 gray																																			
1.00 mm² 06.600.2227.0 red																																			
1.50 mm² 06.600.2327.0 black																																			
Part No.	Std. Pack																																		
0.5 mm² 06.600.3827.0 white																																			
0.75 mm² 06.600.3727.0 gray																																			
1.00 mm² 06.600.3627.0 red																																			
1.50 mm² 06.600.3927.0 black																																			
Part No.	Std. Pack																																		
06.502.4000.0																																			
06.502.4300.0																																			

Mounting plate for distribution blocks 5 pole; 5/3pole only in combination with a mounting plate 3 pole (with mounting flange)	Assignment of components																																		
	<table border="1"> <thead> <tr> <th></th> <th>Distribution block 5 pole 5/3 pole</th> <th colspan="2">Distribution block with mounting flange 3 pole</th> </tr> </thead> <tbody> <tr> <td></td> <td>92.050.0353.1 92.050.0153.1</td> <td>92.030.4853.1 92.030.4853.0 92.030.5353.1 92.030.5353.0</td> <td></td> </tr> <tr> <td>Mounting plates</td> <td>07.413.5653.1</td> <td>07.413.5453.1</td> <td>-</td> </tr> <tr> <td></td> <td>2x</td> <td>-</td> <td>-</td> </tr> <tr> <td></td> <td>1x</td> <td>1x</td> <td>-</td> </tr> <tr> <td></td> <td>-</td> <td>-</td> <td>2x</td> </tr> <tr> <td></td> <td>1x</td> <td>-</td> <td>1x</td> </tr> <tr> <td></td> <td>-</td> <td>1x</td> <td>1x</td> </tr> </tbody> </table>				Distribution block 5 pole 5/3 pole	Distribution block with mounting flange 3 pole			92.050.0353.1 92.050.0153.1	92.030.4853.1 92.030.4853.0 92.030.5353.1 92.030.5353.0		Mounting plates	07.413.5653.1	07.413.5453.1	-		2x	-	-		1x	1x	-		-	-	2x		1x	-	1x		-	1x	1x
	Distribution block 5 pole 5/3 pole	Distribution block with mounting flange 3 pole																																	
	92.050.0353.1 92.050.0153.1	92.030.4853.1 92.030.4853.0 92.030.5353.1 92.030.5353.0																																	
Mounting plates	07.413.5653.1	07.413.5453.1	-																																
	2x	-	-																																
	1x	1x	-																																
	-	-	2x																																
	1x	-	1x																																
	-	1x	1x																																

Crimping tool

**suitable for ferrule crimping
to use in spring clamp
termination**

for ferrules of
0.08 – 6 mm², AWG 28 – 10





- Square crimping
- Releasable interlock
- Adjustable crimping pressure


Total length: 174 mm



Color	Part No.	Std. Pack	Part No.	Std. Pack
black	95.101.1300.0	1		

Accessories

<p>Test connector, 2-fold 230 V input</p> <p>Connector with two switches between pin 1 and N or pin 2 and N; for testing of binary inputs of gesis ELECTRONICS devices, GST 18i4 connectors code 2 dark gray Nominal voltage: 230 V AC</p>	<p>Test connector, single 230 V output</p> <p>Connector with an indicator lamp between L and N, for testing the function of binary outputs of gesis ELECTRONICS devices, GST 18i3 connectors code 1 black Nominal voltage 230 V AC</p>	<p>Test-connector, 2-fold 230 V output</p> <p>Connector with two indicator lamps between pin 1 and N or pin 2 and N, for testing the function of window treatment outputs of gesis ELECTRONICS devices, GST 18i4 connectors code 1 black Nominal voltage: 230 V AC</p>	<p>Test connector, single 230 V S/D output</p> <p>Connector with an indicator lamp between L and N, for testing the function of switching/dimming outputs of gesis ELECTRONICS devices; only the switching output is tested, not the control output; GST 18i5 connector code 2 pastel blue Nominal voltage: 230 V AC</p>																								
																											
<table border="1"> <thead> <tr> <th>Part No.</th> <th>Std. Pack</th> </tr> </thead> <tbody> <tr> <td>92.002.5053.0</td> <td>1</td> </tr> <tr> <td colspan="2">GST 18i4 S 2S GR</td> </tr> </tbody> </table>	Part No.	Std. Pack	92.002.5053.0	1	GST 18i4 S 2S GR		<table border="1"> <thead> <tr> <th>Part No.</th> <th>Std. Pack</th> </tr> </thead> <tbody> <tr> <td>92.002.5153.1</td> <td>1</td> </tr> <tr> <td colspan="2">GST 18i3 S 1H SW</td> </tr> </tbody> </table>	Part No.	Std. Pack	92.002.5153.1	1	GST 18i3 S 1H SW		<table border="1"> <thead> <tr> <th>Part No.</th> <th>Std. Pack</th> </tr> </thead> <tbody> <tr> <td>92.002.5253.1</td> <td>1</td> </tr> <tr> <td colspan="2">GST 18i4 S 2H SW</td> </tr> </tbody> </table>	Part No.	Std. Pack	92.002.5253.1	1	GST 18i4 S 2H SW		<table border="1"> <thead> <tr> <th>Part No.</th> <th>Std. Pack</th> </tr> </thead> <tbody> <tr> <td>92.002.5353.1</td> <td>1</td> </tr> <tr> <td colspan="2">GST 18i5 S 1H SPB</td> </tr> </tbody> </table>	Part No.	Std. Pack	92.002.5353.1	1	GST 18i5 S 1H SPB	
Part No.	Std. Pack																										
92.002.5053.0	1																										
GST 18i4 S 2S GR																											
Part No.	Std. Pack																										
92.002.5153.1	1																										
GST 18i3 S 1H SW																											
Part No.	Std. Pack																										
92.002.5253.1	1																										
GST 18i4 S 2H SW																											
Part No.	Std. Pack																										
92.002.5353.1	1																										
GST 18i5 S 1H SPB																											





Mounting rail 35 x 7,5

according to DIN EN 60715

Steel, galvanically zinc-plated and dichromated



Total length: 200 mm

**Mounting rail 35 x 15**

according to DIN EN 60715

Steel, galvanically zinc-plated and dichromated

Total length: 200 mm

**End bracket for TS 35**

Screw mount

8 mm wide

**End bracket for TS 35**

Screwless mount

8 mm wide



Part No. Std. Pack

Part No. Std. Pack

Part No. Std. Pack

Part No. Std. Pack

unslotted
slotted98.300.0000.0
98.300.1000.0

98.360.0000.0

Z5.522.8553.0

99.488.0000.0

Accessories

Additional accessories of series **fasis/selos** BIT are available in our AT catalog.

