

deburring system

MINI SCRAPER NG3700

Ideal for tool and die makers.

Includes: NG-3 handle, D holder, (an M3 setscrew is holding the blade) triangular mini scraper D50 blade and hex key.



TRIANGULAR SCRAPER NG3600

Used for standard scraping.

Includes: NG-3 handle, T holder (with M5 internal threads) and I.D. 4.2x57mm triangular scraper T70 (with M5 external thread).



HANDLES



NG-3 Handle NG3000

NogaGrip-3 holds all blade holders. Designed for maximum comfort in your hand.



SC Handle SC1300

12mm anodized handle. Knurled locking collar to control blade extension.
Holds: D50, D66, D75, D77 and T80 scrapers.
Length: 120mm.
Hex: 12mm.

HOLDERS



T Holder EL06023

T holder is designed to hold T50 and T70 new scrapers.
Has M5 internal thread.
Length: 113mm



D Holder EL05003


D holder is designed to hold D50 and D66 blades. A 3mm setscrew is holding the blade.
Hex key included.
Length: 131mm.




Pipe Cross Holes



Bushing Scraping



Straight Edge



Holes


SCRAPERS



INTERNAL SCRAPER NG3710

Ideal for cross-holes deburring.

Includes: NG-3 handle, D holder and Internal scraper D66 blade.



ADJUSTABLE SCRAPER SC8000

Ideal for scraping, trimming and deburring almost all materials.

Includes: 12mm anodized handle and T80 double ended triangular scraper.



All blades below have hardness 62-64Rc, except D55 Carbide 1400-1700 HV, and T80 CR115 58-60Rc.

BLADES	Order No.		Dimensions (mm)	Included angle (degrees)	Weight (grams)	Package quantity
D50	BD5010		3.2 x 50	60	27	10
D55 Carbide	BD5501		3.2 x 50	60	9	1
D66	BD6610		3.2 x 48	50	34	10
D75	BD7501		3.2 x 75	60	8	1
D77	BD7701		3.2 x 73	50	9	1
T50	BT5000		I.D3.5 x 51	60	8	1
T70	BT7000		I.D4.2 x 57	60	11	1
T80	BT8001		I.C2.5 X 80	60	11	1