


T-3¼ MINIATURE BAYONET BASE

MINIATURE LAMP

14V .20A

WAMCO PART NO.		ENVELOPE SIZE		BASE TYPE	RATING		FILAMENT SHAPE	
WL-1815		T-3¼		BA9s	14V .20A		C-2V	
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)				LIFE HRS
	MIN	NOM	MAX	MIN	NOM	MAX		
	14V	.180	.200	.220	1.05	1.40	1.75	
					3,000			

DIMENSIONAL CHARACTERISTICS



NOTES

1. LCL = .75" (19mm)
2. Nickel-plated brass construction base
3. Part mark WL-1815
4. RoHS compliant
5. ANSI trade number 1815

