


# T-3¼ MINIATURE BAYONET BASE

## MINIATURE LAMP

55V 50mA

| WAMCO PART NO. |              | ENVELOPE SIZE | BASE TYPE | RATING              | FILAMENT SHAPE |      |          |
|----------------|--------------|---------------|-----------|---------------------|----------------|------|----------|
| WL-1835        |              | T-3¼          | BA9s      | 55V 50mA            | C-2F           |      |          |
| TEST VOLTS     | CURRENT (mA) |               |           | LIGHT OUTPUT (MSCP) |                |      | LIFE HRS |
|                | MIN          | NOM           | MAX       | MIN                 | NOM            | MAX  |          |
| 55V            | 43           | 50            | 58        | .72                 | 1.10           | 1.48 | 5,000    |

## DIMENSIONAL CHARACTERISTICS



## NOTES

1. Nickel-plated brass construction base
2. Part mark WL-1835
3. RoHS compliant
4. ANSI trade number 1835

