


T-3¼ MINIATURE BAYONET BASE

MINIATURE LAMP

5V 90mA

WAMCO PART NO.		ENVELOPE SIZE		BASE TYPE	RATING	FILAMENT SHAPE		
WL-1850		T-3¼		BA9s	5V 90mA	C-2R		
TEST VOLTS	MIN	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS
		NOM	MAX		MIN	NOM	MAX	
5V	81	90	99		.187	.250	.313	1,500

DIMENSIONAL CHARACTERISTICS



NOTES

1. LCL = .63" (16mm)
2. Nickel-plated brass construction base
3. Part mark WL-1850
4. RoHS compliant
5. ANSI trade number 1850

