


# GG-12A AIRCRAFT WARNING LAMP

## SINGLE CONTACT INDEX BAYONET BASE

28V 40W

WAMCO PART NO.		ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE
WL-684		GG-12A	BAY15s	28V 40W	CC-6
TEST VOLTS	CURRENT (A)			LIGHT DISTRIBUTION	LIFE HRS
	MIN	NOM	MAX		
28V	1.32	1.43	1.54	4800 CANDLE POWER MINIMUM ON REFLECTOR AXIS HORIZONTAL AND VERTICAL BEAM SPREAD TO 480 CANDLE POWER, 20° MINIMUM	150

## DIMENSIONAL CHARACTERISTICS



## NOTES

1. Finish clear, except where reflective surface is required
2. Reflective coating must conform to the coating adhesion requirements of MIL-L-6363F, paragraph 4.6.6
3. Reflective coating is isolated from lamp base, clear area between base and start of reflective coating to be  $2.2 \text{ mm} \pm 1 \text{ mm}$
4. Part mark WL-684, 28V, 40W
5. RoHS compliant

