

MG24118

Supplementary Protector , 240VAC, 16A, Circuit Breaker Type: Standard



Technical Characteristics

Specific Application	Protection for sensitive equipment (computers, electronic devices etc.)
Approvals	UL 1077 Recognized, IEC 60947-2 Rated
Circuit Breaker Type	Standard
Ampere Rating	16A
Width	0.71 Inches (18mm)
General Application	Overcurrent protection within appliances or electrical equipment where branch circuit breaker protection is provided or not required
For Use With	OEM Panels
Marketing Trade Name	Multi 9
Voltage Rating	240VAC
Mounting Type	DIN Rail (35mm)
Number of Poles	1-Pole
Weight	3.85 Ounces
Short Circuit Current Rating	10kA@120/240VAC - 5kA@277VAC
Trip Curve	B Curve - Magnetic operates between 3.2 to 4.8 tim
Type	C60N
Wire Size	#14 to #4 AWG (Cu)
Depth	3.00 Inches (76mm)
Height	3.19 Inches (81mm)

Shipping and Ordering

Category	00908 - Supplemental Circuit Protectors, 1 Pole: 15 - 63 Amp, 2 Pole: 1 - 63 Amp, 3 Pole: 1 - 63 Amp, 4 Pole: 1 - 63 Amp, Type Multi 9 C60
Discount Schedule	DE2
GTIN	00785901880189
Package Quantity	1
Weight	0.27 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.