


# T-3¼ MINIATURE BAYONET BASE

## MINIATURE LAMP

6.3V .15A

WAMCO PART NO.		ENVELOPE SIZE		BASE TYPE	RATING	FILAMENT SHAPE	
WL-755		T-3¼		BA9s	6.3V .15A	C-2R	
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS
	MIN	NOM	MAX	MIN	NOM	MAX	
6.3V	.135	.150	.165	.247	.330	.413	20,000

## DIMENSIONAL CHARACTERISTICS



## NOTES

1. LCL = .78" (19.8mm)
2. Nickel-plated brass construction base
3. Part mark WL-755
4. RoHS compliant
5. ANSI trade number 755

