


T-3¼ MINIATURE BAYONET BASE

MINIATURE LAMP

28V 80mA

WAMCO PART NO.		ENVELOPE SIZE		BASE TYPE		RATING		FILAMENT SHAPE	
WL-757		T-3¼		BA9s		28V 80mA		C-2F	
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS		
	MIN	NOM	MAX	MIN	NOM	MAX			
28V	72	80	88	.465	.620	.775	7,500		

DIMENSIONAL CHARACTERISTICS



NOTES

1. LCL = .63" (16mm)
2. Nickel-plated brass construction base
3. Part mark WL-757
4. RoHS compliant
5. ANSI trade number 757

