


500MHz Passive Oscilloscope Probe **TENMA™**

**RoHS
Compliant**



Description:

General purpose series 500MHz, 10x fixed attenuation oscilloscope probe. Probe features a readout actuator pin (sense pin) on the BNC connector.

500MHz (-3 dB) bandwidth

High impedance input (10M Ω /12pF)

9–18 pF compensation range

300 V CAT II

Features:

- Snap-Locking Sprung Hook
- Easily replaceable tip
- Large accessory set
- Meets IEC 61010-031

Specifications:

Type	: 5mm Passive Voltage
Bandwidth	: 500MHz
Attenuation	: 10x
Input Impedance	: 10M Ω
Input Capacitance	: 12pF
Output Impedance	: 1M Ω
Risetime	: 0.7 ns
IEC Rating	: 300 V CAT I
Compensation	: 9–18 pF
Length	: 1.2m
Operating Temperature	: 0° to +50°C
Humidity	: 85% RH or less (at 35°C)

Accessories included : 15cm Ground Lead, 15cm Ground Lead w/0.6mm Jack and IC Clip, Replacement Tip, Black Snap-on Sprung Hook, Tip Insulator, IC Tip, BNC Adapter, 4 pcs. Probe Tip Ground, Deluxe Trimmer Tool, Twin Lead Adapter w/ 2 IC Clips & Identifier Rings.

The High Performance family is a high quality, general purpose set of 5mm Passive Voltage Oscilloscope probes. They are excellent replacement probes for all makes and models of oscilloscopes.

Part Number Table

Description	Part Number
500MHz Passive Oscilloscope Probe	76-150

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.