


Capacitor, ceramic, SMD, MLCC, Array, Flex Termination, Class II, 2200 pF, +/-10% Tol, 0612, 200 V, X7R



General Information	
Supplier:	KEMET
Application:	Standard Array/Flexible Termination
Part Type Description:	SMD, MLCC, Array, Flex Termination, Class II
Temperature Coefficient:	X7R
Body Type:	SMD Array
Termination Type:	Tin (Sn)
Chip Size:	0612
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1.6	+/-0.2
W	3.2	+/-0.2
T	0.8	+/-0.1
P	0.8	+/-0.1

Specifications	
Capacitance:	2200 pF
Voltage:	200 V
Tolerance:	+/-10%
Failure Rate:	N/A

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	4000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.