



TYPE - SLA




Contact your local Sales Representative
[Click Here for Printable Version](#)

Trade Size	Type	Inside Bend Radius	Wt. (lbs) 50 Ft.	Length	Part No.
3/8"	SLA-10	2.0"	14.5 lbs	50 FT	78907
1/2"	SLA-11	3.0"	16 lbs	50 FT	78917
3/4"	SLA-12	4.2"	26.5 lbs	50 FT	78927
1"	SLA-13	5.5"	41 lbs	50 FT	78937
1-1/4"	SLA-14	7.0"	51 lbs	50 FT	78942
1-1/2"	SLA-15	4.5"	62 lbs	50 FT	78952
2"	SLA-16	6.0"	72.5 lbs	50 FT	78962

SHIELDING EFFECTIVENESS:


The graph below depicts a general comparative shielding effectiveness (attenuation in dBs) of all three types of SHIELD-FLEX conduit. The dotted line indicates a comparison to standard unshielded liquidtight flexible conduit Type LA. The spectrum of test frequency is from 1 MHz to 10 MHz Electric Field, to 100 MHz to 1 GHz Planewave Field and 2 GHz to 6 GHz Microwave Field. Tests were performed per MIL-STD-285 on 1" trade size conduit using standard liquidtight fittings from Thomas & Betts Series 5300. Results are based on controlled laboratory conditions and may vary in actual field installed conditions.

Sizes 3/8" - 1-1/4"



Squarelock with Filler

TEST FREQUENCY CHART:



See [Chart for Dimensions and Tolerances](#).

TYPE - SLA

Type SLA is identical to standard UL Listed liquidtight flexible steel conduit (See Type LA) but is augmented with a tinned copper shielding braid located over the inner steel core and under its protective PVC jacket. The braid offers a minimum of 90% coverage.

Shield-Flex, SLA, and HFSLA are trademarks of Electri-Flex Company, registered in the U.S. Patent and Trademark Office.

For a low-smoke, low-flame spread, zero-halogen version, ask for HFSLA

APPLICATION:


This Conduit is intended for installation in accordance with Article 350 of the NEC (ANSI/NFPA-70).

-Suitable as an equipment grounding conductor per Article 250.118(7). Larger sizes require separate grounding conductor.

-Suitable for use in hazardous locations: Class I, Div. 2 and Classes II and III.

-PVC jacket is resistant to a wide variety of oils, acids, alkaline and ultraviolet light.

-Accepts Standard Metallic Liquidtight Fittings

 Listed File # E29278. Conforms UL360 for liquidtight flexible steel conduit.

Tests Include:

[All RoHS and WEEE Compliant](#)

ARRA:

For ARRA Certification Letter, please [click here](#)

STANDARD COLORS:

Black. [Other colors and jacketing materials available upon request](#)

WORKING TEMPERATURES:

-30°C to 80°C Dry / 60°C Wet / 70°C Oil

Flexibility: [See the Flexibility Comparison Guide](#)

Metal Used: Steel

Plastic Used: PVC [See the Chemical Resistance Guide](#)

High Mech. Strength	Listed For Direct Burial	Halogen Free	Low Fire Hazard	Accepts Standard Liquidtight Fittings	Self Extinguish	EMI/RFI Shielding	Oil Resistance	Acid Resistance
X	X			X	X	X	X	X

[Packaging, Disclaimer and Warranty](#)

® Electri-Flex Company 1-800-323-6174

[Privacy](#) [Terms.](#)