



Power Cord, C19 to 5-20P, 2.5m
Part Number: AP9873



[Technical Specifications](#) [Product Overview](#) [Ratings and Reviews](#)

Output

Maximum Total Current Draw per 20A Phase

Output Connections (1) IEC 320 C19



Overload Protection No

Input

Input Frequency 50/60 Hz

Input Connections NEMA 5-20P



Cord Length 8.2 feet (2.50 meters)

Number of Power Cords 1

Acceptable Input Voltage 100-120 VAC

Maximum Line Current per phase 20A

Maximum Input Current per phase 20A

Load Capacity 2400 VA

Physical

Net Weight 0.50 lbs. (0.22 kg)

Maximum Height 2.00 inches (51 mm)

Maximum Width 9.00 inches (229 mm)

Maximum Depth 4.00 inches (102 mm)

Shipping Weight 0.66 lbs. (0.30 kg)

Shipping Height 4.00 inches (102 mm)

Shipping Width	12.50 inches (318 mm)
----------------	-----------------------

Shipping Depth	4.26 inches (108 mm)
----------------	----------------------

Color	Black
-------	-------

Environmental

Operating Environment	32 - 113 °F (0 - 45 °C)
-----------------------	-------------------------

Operating Relative Humidity	0 - 95%
-----------------------------	---------

Operating Elevation	0-10000 feet (0-3000 meters)
---------------------	------------------------------

Storage Temperature	-13 - 149 °F (-25 - 65 °C)
---------------------	----------------------------

Storage Relative Humidity	0 - 95%
---------------------------	---------

Storage Elevation	0-50000 feet (0-15000 meters)
-------------------	-------------------------------

Conformance

Approvals	CSA, UL Listed
-----------	----------------

Standard warranty	2 years repair or replace
-------------------	---------------------------

Sustainable Offer Status

PEP	Available in Documentation tab
-----	--------------------------------

EOLI	Available in Documentation tab
------	--------------------------------

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.