

Technical Data

Issue 06 February 2000

General description

A thin PVC film, coated with a low tack UV resistant adhesive.

- Flame retardant.
- Easy unwind.
- Flexible.
- Conformable to awkward shapes.
- Water resistant.
- Good abrasion resistance.
- UV resistant.
- Non-corrosive adhesive.
- Low tack.
- Clean peel.

Technical Details

Typical values

Thickness	0.13mm
Breaking Load	23 N/cm
Elongation	150%
Adhesion	
Steel	0.30 N/cm
Service Temp	0°C to +60°C
Application Temp	0°C to +40°C

AT44 Low Tack Protection Tape



NOTE

Except where indicated otherwise, the above figures are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The Company reserves the right to improve products and any change in specification will result in a re-issue of the relevant 'Technical Data Sheet'. Customers should satisfy themselves that the tape is suitable for their requirements whether after such modifications or otherwise. Please check that you have the latest issue of the 'Technical Data Sheet'. All slitting and length tolerances are to British Standards. Before use the customer is advised to consult the Health & Safety Data Sheet produced by the company for this product, which is available on request.

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.

 **ADVANCE**
adhesive tapes



BS EN ISO 9002
Q05206



INVESTOR IN PEOPLE

Advance Tapes International Limited, PO Box 122,
Abbey Meadows, Leicester, LE4 5RA.

Tel: 0116 251 0191. Fax: 0116 265 2046. www.advancetapes.com

AFERA

Association des Fabricants Européens de
Rubans Auto-Adhésifs.