

**DOW CORNING(R) 340 HEAT SINK
COMPOUND**

Version 2.0 Revision Date: 06/29/2015 SDS Number: 953200-00002 Date of last issue: 02/09/2015
Date of first issue: 02/09/2015

SECTION 1. IDENTIFICATION

Product name : DOW CORNING(R) 340 HEAT SINK COMPOUND
Product code : 000000000001015443

Manufacturer or supplier's details

Company name of supplier : Dow Corning Corporation
Address : South Saginaw Road
Midland Michigan 48686
Telephone : (989) 496-6000
Emergency telephone : 24 Hour Emergency Telephone : (989) 496-5900
CHEMTREC : (800) 424-9300

Recommended use of the chemical and restrictions on use

Recommended use : Heat transfer agents

SECTION 2. HAZARDS IDENTIFICATION**GHS Classification**

Not a hazardous substance or mixture.

GHS Label element

Not a hazardous substance or mixture.

Other hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture
Chemical nature : Silicone compound

Hazardous ingredients

Chemical Name	CAS-No.	Concentration (%)
Zinc oxide	1314-13-2	>= 50 - < 70

SECTION 4. FIRST AID MEASURES

If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.
In case of skin contact : Wash with water and soap as a precaution.
Get medical attention if symptoms occur.

**DOW CORNING(R) 340 HEAT SINK
COMPOUND**

Version 2.0	Revision Date: 06/29/2015	SDS Number: 953200-00002	Date of last issue: 02/09/2015 Date of first issue: 02/09/2015
----------------	------------------------------	-----------------------------	---

- In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
Get medical attention if symptoms occur.
Rinse mouth thoroughly with water.
- Most important symptoms and effects, both acute and delayed : None known.
- Protection of first-aiders : No special precautions are necessary for first aid responders.
- Notes to physician : Treat symptomatically and supportively.

SECTION 5. FIRE-FIGHTING MEASURES

- Suitable extinguishing media : Water spray
Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
- Unsuitable extinguishing media : None known.
- Specific hazards during fire fighting : Exposure to combustion products may be a hazard to health.
- Hazardous combustion products : Metal oxides
Carbon oxides
Silicon oxides
Formaldehyde
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.
- Special protective equipment for fire-fighters : Wear self-contained breathing apparatus for firefighting if necessary.
Use personal protective equipment.

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Follow safe handling advice and personal protective equipment recommendations.

**DOW CORNING(R) 340 HEAT SINK
COMPOUND**

Version 2.0	Revision Date: 06/29/2015	SDS Number: 953200-00002	Date of last issue: 02/09/2015 Date of first issue: 02/09/2015
----------------	------------------------------	-----------------------------	---

- Environmental precautions : Discharge into the environment must be avoided. Prevent further leakage or spillage if safe to do so. Retain and dispose of contaminated wash water. Local authorities should be advised if significant spillages cannot be contained.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material. For large spills, provide diking or other appropriate containment to keep material from spreading. If diked material can be pumped, store recovered material in appropriate container. Clean up remaining materials from spill with suitable absorbent. Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable. Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

SECTION 7. HANDLING AND STORAGE

- Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
- Local/Total ventilation : Use only with adequate ventilation.
- Advice on safe handling : Handle in accordance with good industrial hygiene and safety practice. Take care to prevent spills, waste and minimize release to the environment.
- Conditions for safe storage : Keep in properly labeled containers. Store in accordance with the particular national regulations.
- Materials to avoid : Do not store with the following product types:
Strong oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Ingredients with workplace control parameters**

Ingredients	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Zinc oxide	1314-13-2	TWA (Respirable fraction)	2 mg/m ³	ACGIH
		STEL (Respirable fraction)	10 mg/m ³	ACGIH
		TWA (Dust)	5 mg/m ³	NIOSH REL

DOW CORNING(R) 340 HEAT SINK COMPOUND

Version 2.0 Revision Date: 06/29/2015 SDS Number: 953200-00002 Date of last issue: 02/09/2015
 Date of first issue: 02/09/2015

		TWA (Fumes)	5 mg/m ³	NIOSH REL
		ST (Fumes)	10 mg/m ³	NIOSH REL
		C (Dust)	15 mg/m ³	NIOSH REL
		TWA (total dust)	15 mg/m ³	OSHA Z-1
		TWA (respirable fraction)	5 mg/m ³	OSHA Z-1
		TWA (Fumes)	5 mg/m ³	OSHA Z-1

Engineering measures : Processing may form hazardous compounds (see section 10).
 Ensure adequate ventilation, especially in confined areas.
 Minimize workplace exposure concentrations.

Personal protective equipment

Respiratory protection : General and local exhaust ventilation is recommended to maintain vapor exposures below recommended limits. Where concentrations are above recommended limits or are unknown, appropriate respiratory protection should be worn. Follow OSHA respirator regulations (29 CFR 1910.134) and use NIOSH/MSHA approved respirators. Protection provided by air purifying respirators against exposure to any hazardous chemical is limited. Use a positive pressure air supplied respirator if there is any potential for uncontrolled release, exposure levels are unknown, or any other circumstance where air purifying respirators may not provide adequate protection.

Hand protection

Remarks : Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
 Safety glasses

Skin and body protection : Skin should be washed after contact.

Hygiene measures : Ensure that eye flushing systems and safety showers are located close to the working place.
 When using do not eat, drink or smoke.
 Wash contaminated clothing before re-use.
 These precautions are for room temperature handling. Use at elevated temperature or aerosol/spray applications may require added precautions.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : paste

Color : white

**DOW CORNING(R) 340 HEAT SINK
COMPOUND**

Version	Revision Date:	SDS Number:	Date of last issue: 02/09/2015
2.0	06/29/2015	953200-00002	Date of first issue: 02/09/2015

Odor	:	none
Odor Threshold	:	No data available
pH	:	Not applicable
Melting point/freezing point	:	No data available
Initial boiling point and boiling range	:	Not applicable
Flash point	:	Not applicable
Evaporation rate	:	Not applicable
Flammability (solid, gas)	:	Not classified as a flammability hazard
Upper explosion limit	:	No data available
Lower explosion limit	:	No data available
Vapor pressure	:	Not applicable
Relative vapor density	:	No data available
Relative density	:	2.0
Solubility(ies)		
Water solubility	:	No data available
Partition coefficient: n-octanol/water	:	No data available
Autoignition temperature	:	No data available
Decomposition temperature	:	No data available
Viscosity		
Viscosity, dynamic	:	Not applicable
Explosive properties	:	Not explosive
Oxidizing properties	:	The substance or mixture is not classified as oxidizing.
Molecular weight	:	No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity	:	Not classified as a reactivity hazard.
------------	---	--

**DOW CORNING(R) 340 HEAT SINK
COMPOUND**

Version	Revision Date:	SDS Number:	Date of last issue: 02/09/2015
2.0	06/29/2015	953200-00002	Date of first issue: 02/09/2015

Chemical stability : Stable under normal conditions.

Possibility of hazardous reactions : Use at elevated temperatures may form highly hazardous compounds.
Can react with strong oxidizing agents.
Hazardous decomposition products will be formed at elevated temperatures.

Conditions to avoid : None known.

Incompatible materials : Oxidizing agents

Hazardous decomposition products
Thermal decomposition : Formaldehyde

SECTION 11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure**

Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Ingredients:**Zinc oxide:**

Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg
Method: OECD Test Guideline 401

Acute inhalation toxicity : LC50 (Rat): > 5.7 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist
Method: OECD Test Guideline 403
Assessment: The substance or mixture has no acute inhalation toxicity

Skin corrosion/irritation

Not classified based on available information.

Ingredients:**Zinc oxide:**

Species: Rabbit
Method: OECD Test Guideline 404
Result: No skin irritation

Serious eye damage/eye irritation

Not classified based on available information.

Ingredients:**Zinc oxide:**

Species: Rabbit

**DOW CORNING(R) 340 HEAT SINK
COMPOUND**

Version	Revision Date:	SDS Number:	Date of last issue: 02/09/2015
2.0	06/29/2015	953200-00002	Date of first issue: 02/09/2015

Result: No eye irritation
Method: OECD Test Guideline 405

Respiratory or skin sensitization

Skin sensitization: Not classified based on available information.

Respiratory sensitization: Not classified based on available information.

Ingredients:**Zinc oxide:**

Test Type: Maximization Test (GPMT)

Routes of exposure: Skin contact

Species: Guinea pig

Method: OECD Test Guideline 406

Result: negative

Germ cell mutagenicity

Not classified based on available information.

Ingredients:**Zinc oxide:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Method: OECD Test Guideline 471
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo
cytogenetic assay)
Species: Rat
Application Route: Inhalation
Method: OECD Test Guideline 474
Result: negative

Carcinogenicity

Not classified based on available information.

IARC No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Reproductive toxicity

Not classified based on available information.

Ingredients:**Zinc oxide:**

Effects on fertility : Test Type: Two-generation reproduction toxicity study

**DOW CORNING(R) 340 HEAT SINK
COMPOUND**

Version 2.0 Revision Date: 06/29/2015 SDS Number: 953200-00002 Date of last issue: 02/09/2015
Date of first issue: 02/09/2015

Species: Rat
Application Route: Ingestion
Method: OECD Test Guideline 416
Result: negative

Effects on fetal development : Test Type: Embryo-fetal development
Species: Hamster
Application Route: Ingestion
Result: negative
Remarks: Based on data from similar materials

STOT-single exposure

Not classified based on available information.

STOT-repeated exposure

Not classified based on available information.

Ingredients:**Zinc oxide:**

Routes of exposure: inhalation (dust/mist/fume)
Assessment: No significant health effects observed in animals at concentrations of 0.2 mg/l/6h/d or less.

Repeated dose toxicity**Ingredients:****Zinc oxide:**

Species: Rat
NOAEL: 1.5 mg/m³
Application Route: inhalation (dust/mist/fume)
Exposure time: 3 m
Method: OECD Test Guideline 413

Aspiration toxicity

Not classified based on available information.

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity****Ingredients:****Zinc oxide:**

Toxicity to fish : LC50 (Oncorhynchus mykiss (rainbow trout)): 330 - 780 µg/l
Exposure time: 96 h
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 6.9 - 16.2 mg/l
Exposure time: 48 h
Method: OECD Test Guideline 202

Toxicity to algae : EC50 (Selenastrum capricornutum (green algae)): 136 µg/l

DOW CORNING(R) 340 HEAT SINK COMPOUND

Version	Revision Date:	SDS Number:	Date of last issue: 02/09/2015
2.0	06/29/2015	953200-00002	Date of first issue: 02/09/2015

	Exposure time: 72 h
	Method: OECD Test Guideline 201
	NOEC (Selenastrum capricornutum (green algae)): 24 µg/l
	Exposure time: 72 h
	Method: OECD Test Guideline 201
M-Factor (Acute aquatic toxicity)	: 1
Toxicity to fish (Chronic toxicity)	: NOEC (Oncorhynchus mykiss (rainbow trout)): 199 µg/l Exposure time: 30 d Remarks: Based on data from similar materials
Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity)	: NOEC (Daphnia magna (Water flea)): 37 µg/l Exposure time: 21 d Remarks: Based on data from similar materials
M-Factor (Chronic aquatic toxicity)	: 1
Toxicity to bacteria	: EC50: 5.2 mg/l Exposure time: 3 h Method: OECD Test Guideline 209 Remarks: Based on data from similar materials

Persistence and degradability

No data available

Bioaccumulative potential

Ingredients:

Zinc oxide:

Bioaccumulation	: Species: Fish
	Bioconcentration factor (BCF): 177

Mobility in soil

No data available

Other adverse effects

No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Resource Conservation and Recovery Act (RCRA)	: This product has been evaluated for RCRA characteristics and does not meet the criteria of hazardous waste if discarded in its purchased form.
---	--

Waste from residues	: Dispose of in accordance with local regulations.
---------------------	--

Contaminated packaging	: Dispose of as unused product.
------------------------	---------------------------------

**DOW CORNING(R) 340 HEAT SINK
COMPOUND**

Version	Revision Date:	SDS Number:	Date of last issue: 02/09/2015
2.0	06/29/2015	953200-00002	Date of first issue: 02/09/2015

Empty containers should be taken to an approved waste handling site for recycling or disposal.

SECTION 14. TRANSPORT INFORMATION**International Regulation****UNRTDG**

UN number	: UN 3077
Proper shipping name	: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc oxide)
Class	: 9
Packing group	: III
Labels	: 9

IATA-DGR

UN/ID No.	: UN 3077
Proper shipping name	: Environmentally hazardous substance, solid, n.o.s. (Zinc oxide)
Class	: 9
Packing group	: III
Labels	: Miscellaneous
Packing instruction (cargo aircraft)	: 956
Packing instruction (passenger aircraft)	: 956

IMDG-Code

UN number	: UN 3077
Proper shipping name	: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc oxide)
Class	: 9
Packing group	: III
Labels	: 9
EmS Code	: F-A, S-F
Marine pollutant	: yes

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

Domestic regulation**49 CFR**

UN/ID/NA number	: UN 3077
Proper shipping name	: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc oxide)
Class	: 9
Packing group	: III

DOW CORNING(R) 340 HEAT SINK COMPOUND

Version	Revision Date:	SDS Number:	Date of last issue: 02/09/2015
2.0	06/29/2015	953200-00002	Date of first issue: 02/09/2015

Labels	: CLASS 9
ERG Code	: 171
Marine pollutant	: yes (Zinc oxide)
Remarks	: Above applies only to containers over 119 gallons or 450 liters., Shipment by ground under DOT is non-regulated; however it may be shipped per the applicable hazard classification to facilitate multi-modal transport involving ICAO (IATA) or IMO.

SECTION 15. REGULATORY INFORMATION

EPCRA - Emergency Planning and Community Right-to-Know

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : No SARA Hazards

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : The following components are subject to reporting levels established by SARA Title III, Section 313:

Zinc oxide	1314-13-2	69 %
------------	-----------	------

US State Regulations

Pennsylvania Right To Know

Zinc oxide	1314-13-2	50 - 70 %
Dimethyl siloxane, trimethylsiloxy-terminated	63148-62-9	30 - 50 %

New Jersey Right To Know

Zinc oxide	1314-13-2	50 - 70 %
Dimethyl siloxane, trimethylsiloxy-terminated	63148-62-9	30 - 50 %

California Prop 65

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

The ingredients of this product are reported in the following inventories:

KECI : All ingredients listed, exempt or notified.

REACH : All ingredients (pre-)registered or exempt.

TSCA : All chemical substances in this material are included on or exempted from listing on the TSCA Inventory of Chemical

DOW CORNING(R) 340 HEAT SINK COMPOUND


Version 2.0 Revision Date: 06/29/2015 SDS Number: 953200-00002 Date of last issue: 02/09/2015
 Date of first issue: 02/09/2015

Substances.

- AICS : All ingredients listed or exempt.
- IECSC : All ingredients listed or exempt.
- ENCS/ISHL : All components are listed on ENCS/ISHL or exempted from inventory listing.
- PICCS : All ingredients listed or exempt.
- DSL : All chemical substances in this product comply with the CEPA 1999 and NSNR and are on or exempt from listing on the Canadian Domestic Substances List (DSL).
- NZIoC : All ingredients listed or exempt.

Inventories

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), TCSI (Taiwan), TSCA (USA)

SECTION 16. OTHER INFORMATION**Further information****NFPA:****HMIS III:**

HEALTH	0
FLAMMABILITY	1
PHYSICAL HAZARD	0

0 = not significant, 1 = Slight,
 2 = Moderate, 3 = High
 4 = Extreme, * = Chronic

Full text of other abbreviations

- ACGIH : USA. ACGIH Threshold Limit Values (TLV)
- NIOSH REL : USA. NIOSH Recommended Exposure Limits
- OSHA Z-1 : USA. Occupational Exposure Limits (OSHA) - Table Z-1 Limits for Air Contaminants
- ACGIH / TWA : 8-hour, time-weighted average
- ACGIH / STEL : Short-term exposure limit
- NIOSH REL / TWA : Time-weighted average concentration for up to a 10-hour workday during a 40-hour workweek

**DOW CORNING(R) 340 HEAT SINK
COMPOUND**

Version	Revision Date:	SDS Number:	Date of last issue: 02/09/2015
2.0	06/29/2015	953200-00002	Date of first issue: 02/09/2015

NIOSH REL / ST	: STEL - 15-minute TWA exposure that should not be exceeded at any time during a workday
NIOSH REL / C	: Ceiling value not be exceeded at any time.
OSHA Z-1 / TWA	: 8-hour time weighted average
Sources of key data used to compile the Material Safety Data Sheet	: Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, http://echa.europa.eu/
Revision Date	: 06/29/2015

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

US / Z8