



Revision Number: 003.0

Issue date: 02/28/2014

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: LOCTITE LB 8423 DIELECTRIC TUNE-UP GREASE known as LOCTITE® DIELECTRIC TUNE-UP G **IDH number:** 495549

Product type: Lubricant **Item number:** 37535

Restriction of Use: None identified **Region:** United States

Company address: Henkel Corporation
One Henkel Way
Rocky Hill, Connecticut 06067 **Contact information:**
Telephone: 860.571.5100
MEDICAL EMERGENCY Phone: Poison Control Center
1-877-671-4608 (toll free) or 1-303-592-1711
TRANSPORT EMERGENCY Phone: CHEMTREC
1-800-424-9300 (toll free) or 1-703-527-3887
Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING: CAUSES SKIN IRRITATION.
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A

PICTOGRAM(S)



Precautionary Statements

Prevention: Wash thoroughly after handling. Wear eye and face protection. Wear protective gloves.
Response: IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.

Storage: Not prescribed
Disposal: Not prescribed

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Silica, amorphous, fumed, crystal-free	112945-52-5	5 - 10
Silicone Resin	Proprietary	60 - 100

IDH number: 495549

Product name: LOCTITE LB 8423 DIELECTRIC TUNE-UP GREASE known as LOCTITE® DIELECTRIC TUNE-UP G

* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If symptoms develop and persist, get medical attention. If breathing is difficult, give oxygen. Get immediate medical attention.
Skin contact:	Wash with soap and water. If symptoms develop and persist, get medical attention.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If eye irritation persists, consult a specialist.
Ingestion:	Do not induce vomiting. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Water should be used to cool closed containers to prevent pressure build-up and possible autoignition or explosion when exposed to extreme heat. Wear a self-contained breathing apparatus with a full face piece operated in pressure-demand or other positive pressure mode.
Unusual fire or explosion hazards:	None
Hazardous combustion products:	Oxides of carbon.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Ventilate area. Do not allow product to enter sewer or waterways.
Clean-up methods:	Scrape up spilled material and place in a closed container for disposal.

7. HANDLING AND STORAGE

Handling:	Avoid contact with eyes, skin and clothing. Use only with adequate ventilation.
Storage:	Keep away from heat, spark and flame. Keep in a cool, well ventilated area.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Silica, amorphous, fumed, crystal-free	10 mg/m3 TWA Inhalable dust. 3 mg/m3 TWA Respirable fraction.	20 MPPCF TWA 0.8 mg/m3 TWA	None	None
Silicone Resin	None	None	None	None

Engineering controls:	Use local ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s). Observe OSHA regulations for respirator use (29 CFR 1910.134).
Eye/face protection:	Safety goggles or safety glasses with side shields.
Skin protection:	Chemical resistant, impermeable gloves. Use of Butyl or Nitrile Rubber gloves is recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid
Color:	Clear
Odor:	Mild
Odor threshold:	Not available.
pH:	Not applicable
Vapor pressure:	< 5 mm hg (77 °F (25°C))
Boiling point/range:	> 300 °F (> 148.9 °C) None
Melting point/ range:	Not available.
Specific gravity:	0.86
Vapor density:	Heavier than air.
Flash point:	> 260 °C (> 500°F) HST-US D09F; Flash/Fire Point By Cleveland Open Cup
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not determined
Evaporation rate:	Not available.
Solubility in water:	Not available.
Partition coefficient (n-octanol/water):	More soluble in octanol.
VOC content:	0 %; 0 g/l
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable at normal conditions.
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Formaldehyde. Oxides of carbon.
Incompatible materials:	Strong acids and strong bases. Strong oxidizing agents.
Reactivity:	Not available.
Conditions to avoid:	Heat, flames, sparks and other sources of ignition.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure:	Ingestion
-------------------------------------	-----------

Potential Health Effects/Symptoms

Inhalation: When heated to temperatures exceeding 300° F (150° C) in the presence of air, silicones may form formaldehyde vapors. Formaldehyde is a potential cancer hazard and a known skin and respiratory sensitizer. Vapors irritate the eyes, nose and throat. Safe handling conditions may be maintained by keeping formaldehyde vapor concentrations below the OSHA permissible limit. Mist or spray may cause respiratory tract irritation and delayed onset pulmonary edema.

Skin contact: Causes skin irritation.

Eye contact: Causes serious eye irritation.

Ingestion: Not expected under normal conditions of use.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Silica, amorphous, fumed, crystal-free	None	Nuisance dust
Silicone Resin	None	Irritant

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Silica, amorphous, fumed, crystal-free	No	No	No
Silicone Resin	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status:	All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification:	None above reporting de minimis
CERCLA/SARA Section 302 EHS:	None above reporting de minimis
CERCLA/SARA Section 311/312:	Immediate Health
CERCLA/SARA Section 313:	None above reporting de minimis
California Proposition 65:	This product contains a chemical known in the State of California to cause cancer.

Canada Regulatory Information

CEPA DSL/NDSL Status:	All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
------------------------------	---

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Catherine Bimler, Regulatory Affairs Specialist

Issue date: 02/28/2014

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.