

BMXP341000

processor module M340 - max 512 discrete + 128
analog I/O - Modbus



Product availability: Stock - Normally stocked in distribution facility

Price*: 878.00 USD



Main

Commercial Status	Commercialised
Range of product	Modicon M340 automation platform
Product or component type	Processor module
Number of racks	2
Number of slots	11
Discrete I/O processor capacity	512 I/O single-rack configuration
Analogue I/O processor capacity	128 I/O multi-rack configuration 66 I/O single-rack configuration
Number of application specific channel	20
Monitoring	Event counters Modbus Diagnostic counters Modbus

Complementary

Control channels	Programmable loops
Integrated connection type	USB port 12 Mbit/s Non isolated serial link RJ45 Modbus master/slave RTU/ASCII asynchronous in baseband RS485 half duplex 0.3...19.2 kbit/s 1 twisted shielded pair Non isolated serial link RJ45 Modbus master/slave RTU/ASCII asynchronous in baseband RS232C half duplex 0.3...19.2 kbit/s 1 twisted shielded pair Non isolated serial link RJ45 character mode asynchronous in baseband RS485 half duplex 0.3...19.2 kbit/s 1 twisted shielded pair Non isolated serial link RJ45 character mode asynchronous in baseband RS232C full duplex 0.3...19.2 kbit/s 2 twisted shielded pairs
Communication module processor	2 AS-Interface module 2 Ethernet communication module
Number of devices per segment	0...32 Modbus 0...32 character mode
Number of devices	2 point-to-point Modbus 2 point-to-point character mode
Bus length	0...49.21 ft (0...15 m) Modbus point-to-point 0...49.21 ft (0...15 m) character mode point-to-point 0...3280.84 ft (0...1000 m) serial link isolated Modbus segment 0...3280.84 ft (0...1000 m) serial link isolated character mode segment 0...32.81 ft (0...10 m) serial link non isolated Modbus segment 0...32.81 ft (0...10 m) serial link non isolated character mode segment
Tap links length	0...131.23 ft (0...40 m) serial link isolated Modbus segment 0...131.23 ft (0...40 m) serial link isolated character mode segment 0...49.21 ft (0...15 m) serial link non isolated Modbus segment 0...49.21 ft (0...15 m) serial link non isolated character mode segment
Number of addresses	0...248 Modbus 0...248 character mode
Requests	504 data bytes per ASCII request Modbus 252 data bytes per RTU request Modbus 1 K data bytes per request character mode

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Control parameter	One LRC on each frame (ASCII) Modbus One LRC on each frame (ASCII) character mode One CRC on each frame (RTU) Modbus
Memory description	Supplied memory card (BMXRMS008MP) for backup of programs, constants, symbols and data 1792 kB internal RAM for program constants and symbols 128 kB internal RAM for data 2048 kB internal RAM
Maximum size of object areas	32760 %KWi constant words located internal data 32464 %MWi internal words located internal data 16250 %Mi located internal bits 128 kB unlocated internal data
Default size of object areas	512 %MWi internal words located internal data 256 %Mi located internal bits 128 %KWi constant words located internal data
Application structure	1 cyclic/periodic master task 1 periodic fast task 32 event tasks No auxiliary task
Execution time per instruction	1.74 µs floating points 0.38 µs single-length words 0.26 µs double-length words 0.18 µs Boolean
Number of instructions per ms	5.4 Kinst/ms 100 % Boolean 4.2 Kinst/ms 65 % Boolean + 35 % fixed arithmetic
System overhead	1.05 ms master task 0.2 ms fast task
Current consumption	72 mA 24 V DC
Supply	Internal power supply via rack
Marking	CE
Status LED	1 LED yellow activity on Modbus (SER COM) 1 LED red processor or system fault (ERR) 1 LED red memory card fault (CARD ERR) 1 LED red I/O module fault (I/O) 1 LED green processor running (RUN)
Product weight	0.44 lb(US) (0.2 kg)

Environment

Ambient air temperature for operation	32...140 °F (0...60 °C)
Relative humidity	10...95 % without condensation
IP degree of protection	IP20
Protective treatment	TC
Standards	CSA C22.2 No 142 EN 61131-2 IEC 61131-2 UL 508 CSA C22.2 No 213 Class I Division 2

Ordering and shipping details

Category	18160 - MODICON M340
Discount Schedule	PC34
GTIN	00785901476368
Nbr. of units in pkg.	1
Package weight(Lbs)	0.52
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0722 - Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - go to CaP for more details
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------