





REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	01/15/09	T. Y.
B	Added R/Y & A/G LED Specs	05/06/10	T. Y.
C	Added LED Specs	02/10/15	J. C.



Recommended Mounting
Hole Size = $\varnothing.032^{+.003}_{-.002}$



SHORT LEAD CATHODE	PART NO.	LONG LEAD CATHODE
RED	3BCC-X	GREEN
YELLOW	3BCC-Y/G-X	GREEN
RED	3BCC-R/Y-X	YELLOW
AMBER	3BCC-A/G-X	GREEN

ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

REVERSE VOLTAGE _____	5V
REVERSE CURRENT _____	100µA
OPERATING TEMPERATURE RANGE _____	-25°C - 85°C
STORAGE TEMPERATURE _____	-30°C - 100°C
LEAD SOLDERING TEMPERATURE(1/16" FROM BODY) _____	260°C FOR 5 SECONDS



STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)	
DECIMALS	ANGULAR
.X ± .1	X° ± 1°
.XX ± .02	
.XXX ± .010	
DESIGNED: Raffy Paje	DATE: 01/15/09
CHECKED: F. Jensen	DATE: 01/15/09

BIVAR®
4 THOMAS, IRVINE, CA. 92618
TEL: (949) 951-8808 FAX: (949) 951-3974

TITLE: T1 (3mm) BI-COLOR LED	
PART NO: 3BCC-XX-X	REVISION: C
CAGE CODE : 32559	SHEET # 1 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.	

SEE SHEET #1		

LED Part No.	Chip			Lens Appearance	Absolute Max. Ratings				Electro-Optical Data @ 20mA			Viewing Angle 2 θ 1/2 (Deg)
	Material	Peak Wave Length λ_p (nm)	Emitted Color		$\Delta\lambda$ (nm)	Pd (mW)	If (mA)	Peak If(mA)	Vf (V)		Iv (mcd)	
									Typ.	Max.	Typ.	
3BCC	GaAsP/GaP	625	RED	WATER CLEAR	35	80	30	150	2.0	2.8	10	40
	GaP/GaP	568	GREEN		30	80	30	150	2.1	2.8	10	40
3BCC-F	GaAsP/GaP	625	RED	WATER CLEAR	35	80	30	150	2.0	2.8	8	40
	GaP/GaP	568	GREEN		30	80	30	150	2.1	2.8	8	40
3BCC-Y/G	GaAsP/GaP	590	YELLOW	WATER CLEAR	35	80	30	150	2.0	2.8	4	40
	GaP/GaP	568	GREEN		30	80	30	150	2.1	2.8	6	40
3BCC-Y/G-F	GaAsP/GaP	590	YELLOW	WATER CLEAR	35	80	30	150	2.0	2.8	6	40
	GaP/GaP	568	GREEN		30	80	30	150	2.1	2.8	8	40
3BCC-R/Y	GaAsP/GaP	625	RED	WATER CLEAR	35	80	30	150	2.0	2.8	8	40
	GaP/GaP	590	YELLOW		30	80	30	150	2.0	2.8	6	40
3BCC-R/Y-F	GaAsP/GaP	625	RED	WATER CLEAR	35	80	30	150	2.0	2.8	8	40
	GaP/GaP	590	YELLOW		30	80	30	150	2.0	2.8	6	40
3BCC-A/G	GaAsP/GaP	605	AMBER	WATER CLEAR	35	80	30	150	2.0	2.8	6	40
	GaP/GaP	568	GREEN		30	80	30	150	2.1	2.8	8	40
3BCC-A/G-F	GaAsP/GaP	605	AMBER	WATER CLEAR	35	80	30	150	2.0	2.8	6	40
	GaP/GaP	568	GREEN		30	80	30	150	2.1	2.8	8	40

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) DECIMALS ANGULAR		 BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974		
				TITLE: T1 (3mm) BI-COLOR LED
DESIGNED: Raffy Paje	DATE: 01/15/09	PART NO: 3BCC-XX-X		REVISION: C
CHECKED: F. Jensen	DATE: 01/15/09	CAGE CODE : 32559		SHEET # 2 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.				