

The MVS Hazer is a versatile and high specification hazer fulfilling the majority of applications where higher volumes of haze are required.

Two variable speed high power fans control the projection and direction of the haze stream (0-90 degrees). The MVS also incorporates a unique oscillating mode with automated back and forth sweeping of the projected haze.

Onboard DMX and the ability to position the unit at any angle complete this fully featured unit.

The MVS uses Le Maitre's sugar based haze fluid which produces fantastic fine, pure and consistent haze that is completely safe to use on stages.

Visit our website for further information, photos and videos

www.lemaitreltd.com

FEATURES

- High continuous haze output
- Dual high power variable speed fans with output up to 125 cbm/hr
- Advanced projection control for accurate wide range
- Oscillating haze projection (0-90 degrees)
- Low fluid consumption: up to 80cc/hr (31 hrs/2.5L bottle)
- Multi-function control panel with data storage
- Onboard 4-channel DMX 512
- Rugged mounting bracket
- Automatic self-cleaning on power-up
- Quiet operation
- Safe for use on live stage performances
- Optional flight case
- Warranty 12 months*
- Made in the UK

* Use of fluids other than Le Maitre will invalidate the warranty

SPECIFICATION

SIZE (mm): 340(H) x 160(W) x 340(L) **POWER:** 230V; 50/60Hz; 300W; 3A

WEIGHT: 12kg **FLUID:** Haze

ACCESSORIES: Bottle Carrier

All Le Maitre hazers incorporate the patented S.T.A.R technology, which uses a two-stage low mass heat exchanger technique to produce a fine, pure and consistent haze that hangs in the air for a long period of time. The result is some of the best haze for lighting operators, providing high definition to aerial beams, adding significantly to the impact and drama of lighting and laser rigs.