## **QTC4 Series**

1.5x4.1 SMD Tuning Fork

#### **Features**

• Low frequency in small size SMD

**General Specifications** 

Frenquency Tolerance at 25°C

Temperature Range (Operating)

Temperature Coefficient

Storage Temperature

Load Capacitance C<sub>L</sub>
Shunt Capacitance C<sub>0</sub>

Drive Level

Aging per Year

**Quality Factor** 

Capacitance Ratio

Motional Capacitance C<sub>1</sub>

Insulation Resistance (M $\Omega$ )

Equivalent Series Resistance (ESR)

**Nominal Frequency** 

- Seam sealed ceramic package offers excellent environmental & heat resistance
- Extended temperature -40 to +85°C for industrial applications

### **Applications**

32.768kHz

±20ppm

-40 to +85°C

-55 to +125°C

7pF, 9pF, 12.5pF

1.7pF typ.

3.0fF typ.

65Κ $\Omega$  max.

1µW max.

±3ppm max.

70000 typ.

450 typ.


500 at 100Vdc ±15Vdc

-0.034 ± 0.008ppm/∆ °C2


- Commercial and Industrial applications
- Wireless communications
- PDA and Smartphone
- Time of day applications







Part Numbering Guide								
Qantek Code	Package	Nominal Frequency (in kHz)	Load Capacitance	Operating Temperature Range	Frequency Tolerance	Packaging		
Q = Qantek	TC4 = 1.5x4.1 SMD Tuning Fork	32.768	07 = 7pF 09 = 9pF <b>12 = 12.5pF</b>	B = -40 to +85°C	1 = ±10ppm 2 = ±20ppm 3 = ±30ppm	R = 3000pcs Tape&Reel		
Example: QTC432.76812B2R bold letters = recommended standard specification								







# QTC4 Series 1.5x4.1 SMD Tuning Fork

### **Marking Code Guide**

Contains manufacturer code / lot code



## Frequency vs. Temperature Characteristics



To calculate the frequency stability the parabolic curvature constant (K) is needed. For calculating the stability at 45°C?

- 1- Change in temperature ( $\Delta T$ ) is (45-25) = +20°C
- 2- Change in frequency is  $(-0.034 \text{ x} (\Delta^{\circ}\text{C})^2) = (-0.035 \text{ x} (20)^2 = -13.6 \text{ppm}$



Phone: +1 877-227-0440 (tollfree) www. Fax: +1 877-227-0440 (tollfree) info