


# APHM-065-05-15

## Micro Peltier cooler module

### Data sheet



$I_{max}$	[A]	0.8
$V_{max}$	[Vdc]	8.3
$P_c \text{ max}$	[W]	4.2
$\Delta T_{max}$	[°C]	74
A	[mm]	11
A1	[mm]	12
B	[mm]	11
B1	[mm]	12
H	[mm]	3.0
L	[mm]	100

- (At hot side temperature  $T_h = 25^\circ\text{C} / 298\text{K}$ , under dry  $\text{N}_2$ )
- $P_c \text{ max}$  = Cooling power at  $\Delta T = 0$  and  $I = I_{max}$
- $\Delta T_{max}$  = Temperature difference at  $I = I_{max}$  and  $P_c = 0$
- Max hot side temperature  $T_h \leq 150^\circ\text{C}$  for best long term performance
- Max mounting pressure: 1.5MPa
- Wires: UL-style 1569,  $105^\circ\text{C}$  (Unstripped)
- Silicone sealed




# APHM-065-05-15

## Micro Peltier cooler module


# APHM-065-05-15

## Micro Peltier cooler module

Data sheet - At hot side temperature 27°C



Data sheet - At hot side temperature 50°C



\*Note - Waste heat = Heat out of hot side


\*Note - Waste heat = Heat out of hot side



# APHM-065-05-15

## Micro Peltier cooler module

Data sheet - At hot side temperature 75°C



\*Note - Waste heat = Heat out of hot side

