


AP2-162-1420-1118

2-stage, Peltier cooler module

Data sheet



I _{max}	[A]	7.8
V _{max}	[Vdc]	16.0
P _c max	[W]	29.3
ΔT _{max}	[°C]	95
A	[mm]	40
A ₁	[mm]	40
B	[mm]	30
B ₁	[mm]	30
H	[mm]	7.6
L	[mm]	100





- (At hot side temperature Th = 25°C / 298K, under dry N₂)
- P_c max = Cooling power at ΔT = 0 and I = I_{max}
- ΔT_{max} = Temperature difference at I = I_{max} and P_c = 0
- Max hot side temperature Th = 90°C for best long term performance
- Max mounting pressure: 1.5MPa
- Wires: UL-style 1569, 105°C (Unstripped)
- Silicone sealed



AP2-162-1420-1118

2 stage, Peltier cooler module

Data sheet - At hot side temperature 27°C







*Note - Waste heat = Heat out of hot side



AP2-162-1420-1118

2 stage, Peltier cooler module

Data sheet - At hot side temperature 50°C




*Note - Waste heat = Heat out of hot side



AP2-162-1420-1118

2 stage, Peltier cooler module

Data sheet - At hot side temperature 75°C



*Note - Waste heat = Heat out of hot side

