

## General Information

Extended Product Type:	CK1-11
Product ID:	1SAM301901R1001
EAN:	4013614403927
Catalog Description:	CK1-11 Short Circuit Signaling Contact
Long Description:	CK1-11 Short-Circuit Signal Contact 2 NO

## Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

## Ordering

EAN:	4013614403927
Minimum Order Quantity:	2 piece
Customs Tariff Number:	85365080

## Container Information

Package Level 1 Width:	25 mm
Package Level 1 Length:	80 mm
Package Level 1 Height:	93 mm
Package Level 1 Gross Weight:	0.08 kg
Package Level 1 EAN:	4013614481529
Package Level 1 Units:	2 piece

## Dimensions

Product Net Width:	9 mm
Product Net Height:	90 mm
Product Net Depth:	78 mm
Product Net Weight:	0.035 kg

## Technical

Rated Operational Voltage:	690 V AC 600 V DC
Rated Operational Current AC-15 (I <sub>e</sub> ):	(24 V) 6 A (240 V) 4 A (380 / 400 V) 3 A (690 V) 1 A
Rated Operational Current DC-13 (I <sub>e</sub> ):	(24 V) 2 A (125 V) 0.55 A (250 V) 0,27 A (440 V) 0.15 A (600 V) 0.15 A
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	Auxiliary Circuit 6 kV
Rated Insulation Voltage (U <sub>i</sub> ):	690 V
Connecting Capacity-Auxiliary Circuit:	Rigid 1/2x 1 ... 1.5 mm <sup>2</sup> Flexible with Ferrule 1/2x 0.75 ... 1.5 mm <sup>2</sup> Flexible with Insulated Ferrule 1/2x 0.75 ... 1.5 mm <sup>2</sup> Flexible 1/2x 0.75 ... 1.5 mm <sup>2</sup>
Tightening Torque:	Auxiliary Circuit 0.8 ... 1.2 N·m
Wire Stripping Length:	Auxiliary Circuit 8 mm
Recommended Screw Driver:	Pozidriv 2 M3
Number of Auxiliary Contacts NO:	1
Number of Auxiliary Contacts NC:	1
Standards:	IEC/EN 60947-1 IEC/EN 60947-2 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 508 CSA 22.2 No. 14
Product Name:	Short Circuit Signaling Contact
Suitable For:	MS132
Suitable for Product Class:	Manual Motor Starter

## Environmental

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Auxiliary Circuit UL/CSA:	Stranded 1/2x 16 ... 14 AWG Flexible 1/2x 16 ... 14 AWG
Tightening Torque UL/CSA:	Auxiliary Circuit 7 in-lb
Contact Rating UL/CSA:	B600 Q600

## Certificates and Declarations (Document Number)

ABS Certificate:	1SAA963001-0101
CB Certificate:	1SAA963001-2002
CCC Certificate:	1SAA963003-3802
cUL Certificate:	cUL_E137861
Declaration of Conformity - CE:	1SAD938501-0188 1SAD938508-0125
DNV Certificate:	1SAA963001-0303
GL Certificate:	1SAA963001-0401
LR Certificate:	1SAA963001-0502
RINA Certificate:	1SAA963000-0802
RoHS Information:	1SAA963002-4405
UL Certificate:	UL_E137861

## Classifications

eClass: 7.0 27379201

