

Americas

Atlanta - 678-957-9614
Austin - 512-257-3370
Boston - 774-760-0087
Chicago - 630-285-0071
Cleveland - 216-447-0464
Dallas - 972-818-7423
Detroit - 248-848-4000
Houston - 281-894-5983
Indianapolis - 317-773-8323
Los Angeles - 949-462-9523
New York - 631-435-6000
Phoenix - 480-792-7200
Santa Jose - 408-735-9110
Toronto - 905-673-0699

Asia/Pacific

Australia - Sydney - 61-2-9868-6733
China - Beijing - 86-10-8569-7000
China - Chengdu - 86-28-8665-5511
China - Chongqing - 86-23-8980-9588
China - Hangzhou - 86-571-8792-8115
China - Hong Kong SAR - 852-2943-5100
China - Nanjing - 86-25-8473-2460
China - Qingdao - 86-532-8502-7355
China - Shanghai - 86-21-5407-5533
China - Shenyang - 86-24-2334-2829
China - Shenzhen - 86-755-8864-2200
China - Wuhan - 86-27-5980-5300
China - Xiamen - 86-592-2388138
China - Xian - 86-29-8833-7252
China - Zhuhai - 86-756-3210040
India - Bangalore - 91-80-3090-4444
India - New Delhi - 91-11-4160-8631
India - Pune - 91-20-3019-1500
Japan - Osaka - 81-6-6152-7160
Japan - Tokyo - 81-3-6880-3770
Korea - Daegu - 82-53-744-4301
Korea - Seoul - 82-2-554-7200
Malaysia - Kuala Lumpur - 60-3-6201-9857
Malaysia - Penang - 60-4-227-8870
Philippines - Manila - 63-2-634-9065
Singapore - 65-6334-8870
Taiwan - Hsin Chu - 886-3-5778-366
Taiwan - Kaohsiung - 886-7-213-7830
Taiwan - Taipei - 886-2-2508-8600
Thailand - Bangkok - 66-2-694-1351

Europe

Austria - Weis - 43-7242-2244-39
Denmark - Copenhagen - 45-4450-2828
France - Paris - 33-1-69-53-63-20
Germany - Dusseldorf - 49-2129-3766400
Germany - Munich - 49-89-627-144-0
Germany - Pforzheim - 49-7231-424750
Italy - Milan - 39-0331-742611
Italy - Venice - 39-049-7625286
Netherlands - Drunen - 31-416-690399
Poland - Warsaw - 48-22-3325737
Spain - Madrid - 34-91-708-08-90
Sweden - Stockholm - 46-8-5090-4654
UK - Wokingham - 44-118-921-5800

03/25/14

MRF24J40MA/MD PICtail™/PICtail Plus Daughter Board

Overview

The MRF24J40MA/MD PICtail™/PICtail Plus Daughter Board is a demonstration and development daughter board for the following modules:

- MRF24J40MA IEEE 802.15.4 2.4 GHz RF Transceiver module (AC164134-1)
- MRF24J40MD 2.4 GHz IEEE 802.15.4 20 dBm RF Transceiver module (AC164134-3)

The daughter board can plug into multiple Microchip Technology demonstration and development boards. For example, the board is appropriate for 8-bit microcontroller development using the PIC18 Explorer Board (DM183032) or for 16-bit microcontroller development using the Explorer 16 Development Board (DM240001).

User's Guide

The **MRF24J40MA/MD PICtail/PICtail Plus Daughter Board User's Guide (DS50001867)** is available for download at <http://www.microchip.com/wireless>. The User's Guide contains more detailed information on the features, operation, schematics and the PCB (Printed Circuit Board).

Software

Sample source code is available from the Microchip Wireless Design Environment: Microchip Wireless Media Access Controller (MiMAC) and Microchip Wireless Application Programming Interface (MiApp), as described in application notes AN1283 and AN1284, respectively. A Quick Start Guide is included in the software installation package that explains the installation and operation of the demonstration program. The Quick Start Guide is available for download from the Microchip web site <http://www.microchip.com/wireless>.

Operation

Programming and configuration options for the MRF24J40MA and MRF24J40MD transceiver modules are provided in the **MRF24J40 IEEE 802.15.4 2.4 GHz RF Transceiver Data Sheet (DS30009776)**. Sample source code is the best place to start. Refer to the compile options when enabling the MRF24J40MA and MRF24J40MD transceiver modules.

IMPORTANT

The MRF24J40MD module contains a power amplifier (PA) and low noise amplifier (LNA). It is important that the MRF24J40 be configured to control the PA and LNA. Refer to **Section 4.2 External PA/LNA Control** in the *MRF24J40 IEEE 802.15.4 2.4 GHz RF Transceiver Data Sheet (DS30009776)*. When using the sample source code, refer to the compile options to enable the PA and LNA.

CAUTION

Voltage and current to the MRF24J40MA/MD PICtail/PICtail Plus Daughter Board should be in the range of 2.4-3.6V and capable of supplying 130 mA. Ensure that the daughter board is plugged into a development/demonstration board that meets this power requirement; otherwise, damage to the MRF24J40 may occur.



Microchip Technology Inc. • 2355 West Chandler Blvd. • Chandler, AZ 85224-6199
www.microchip.com

The Microchip name and logo and the Microchip logo are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries. PICtail is a trademark of Microchip Technology Incorporated in the U.S.A. and other countries. All other trademarks mentioned herein are property of their respective companies.

© 2009-2014, Microchip Technology Incorporated, Printed in the U.S.A. All Rights Reserved. 9/14

DS50001870B

Jumper Configuration

Power Disconnect/Current Measure Jumpers (JP1/JP2) – Two, 2-pin headers are connected in parallel. A shunt connects power to the MRF24J40 module. A current meter can be placed on the header and the shunt removed to measure current consumption.

TIP: To prevent power interruption to the MRF24J40 module, keep the shunt on the header while connecting the current meter. Once connected, remove the shunt to measure current.

INT2 Jumper (JP3) – For the PIC18 Explorer Board, jumpering JP3 with a shunt allows the connection of RA5 to RB2/INT2 and enables push-button switch S2 to trigger an interrupt.