

S1-M3-25

ABB contact for United States of America [View..](#) [Print to Pdf..](#)

General Information

Extended Product Type:	S1-M3-25
Product ID:	1SAM201907R1103
EAN:	4013614400827
Catalog Description:	S1-M3-25 Power Infeed Block
Long Description:	S1-M3-25 3-phase power infeed block Flat, for MS116 / MS132, 25mm ² , Type E



Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

Ordering

EAN:	4013614400827
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369010

Container Information

Package Level 1 Width:	59 mm
Package Level 1 Length:	245 mm
Package Level 1 Height:	38 mm
Package Level 1 Gross Weight:	0.45 kg
Package Level 1 EAN:	4013614488207
Package Level 1 Units:	10 piece

Dimensions

Product Net Width:	43.8 mm
Product Net Height:	43.95 mm
Product Net Depth:	32 mm
Product Net Weight:	0.042 kg

Technical

Rated Operational Voltage:	690 V
Rated Operational Current (I_e):	65 A
Degree of Protection:	IP20
Connecting Capacity-Main Circuit:	Rigid 1x 6 ... 25 mm ² Flexible 1x 6 ... 16 mm ²
Tightening Torque:	Main Circuit 2.5 N·m
Wire Stripping Length:	Main Circuit 10 mm
Recommended Screw Driver:	Pozidriv 2 M3.5
Standards:	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1
Product Name:	Power Infeed Block
Suitable For:	MS116 MS132

Suitable for Product Class: Manual Motor Starter

Environmental

Ambient Air Temperature: Operation -25 +70 °C
Storage -50 ...+80 °C

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Maximum Operating Voltage Main Circuit 600 V

UL/CSA:

Ampere Rating UL/CSA: 65 A

Connecting Capacity Main Circuit Stranded 1/2x 10 ... 4 AWG

UL/CSA: Flexible 1/2x 10 ... 6 AWG

Tightening Torque UL/CSA: Main Circuit 22 in-lb

Certificates and Declarations (Document Number)

cUL Certificate: 1SAA963001-1701

Declaration of Conformity - CE: 1SAD938509-0056

GOST Certificate: 1SAA937000-2703

RoHS Information: 1SAA963003-4402

UL Certificate: 1SAA963001-1602

Classifications

eClass: 7.0 27379201

E-nummer: 3112082

Object Classification Code: X
