

Flush-type connector - SACC-E-M12MSS-3P-M16/0,5 PE - 1411655


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Flush-type connector, Power, 3-position, SocketLink:M12, S power, Front mounting, M16 x 1.5, Individual wires, Cable length: 0.5 m



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 936705
Weight per Piece (excluding packing)	42.1 g
Custom tariff number	85366990
Country of origin	Germany
Product key	ABQEAA
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length of cable	0.5 m
-----------------	-------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 105 °C (Plug / socket)
	-40 °C ... 105 °C (without mechanical actuation)
Degree of protection	IP67

General

Note	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Rated current at 40°C	16 A
Rated voltage	630 V
Rated surge voltage	2 kV
Number of positions	3

Flush-type connector - SACC-E-M12MSS-3P-M16/0,5 PE - 1411655

Technical data

General

Insulation resistance	≥ 100 MΩ
Coding	S power
Standards/regulations	M12 connector
Signal type/category	Power
Status display	No
Overvoltage category	III
Pollution degree	3
Connection method	Individual wires
Insertion/withdrawal cycles	> 100
Torque	3 Nm ... 4 Nm (M12 connector)
Mounting type	Front mounting M16 x 1.5

Material

Flammability rating according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA
Material, knurls	CuZn alloy, nickel-plated
Sealing material	FKM

Cable

Cable type	PP litz wire
Conductor cross section	1.5 mm ²
AWG signal line	16
Wire colors	black 1, black 2, green/yellow
Material conductor insulation	PP
Conductor material	Bare Cu litz wires
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)
	-30 °C ... 90 °C (cable, flexible installation)

Standards and Regulations

Standard designation	M12 connector
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 8.0	27440103

Flush-type connector - SACC-E-M12MSS-3P-M16/0,5 PE - 1411655

Classifications

ETIM

ETIM 4.0	EC002061
ETIM 5.0	EC002061

Approvals

Approvals


Approvals


UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approvals submitted

Approval details

UL Listed 	
mm ² /AWG/kcmil	16
Nominal current I _N	12 A
Nominal voltage U _N	600 V

cUL Listed 	
mm ² /AWG/kcmil	16
Nominal current I _N	12 A
Nominal voltage U _N	600 V

cULus Listed 	
--	--

Accessories

Accessories

Flat nut

Flush-type connector - SACC-E-M12MSS-3P-M16/0,5 PE - 1411655

Accessories

Flat nut - SACC-E-MU-M16 - 1504097



Flat nut with M16 thread


Drawings

Schematic diagram




Pin assignment of M12 plug, 3-pos., S-coded, view of pin side

Dimensional drawing




M12 flush-type plug

Circuit diagram



Contact assignment of the M12 plug

Diagram



Derating diagram