# San Ace 92WF

25mm thick (9WF type), 32mm thick (9WF type)

#### General Specifications

· Material · · · · · Frame: Plastics (Flammability: UL94V-0),

Impeller: Plastics (Flammability: UL94V-0)

· Expected Life ······Refer to specifications (L10:Survival rate: 90% at 60°C ,

rated voltage, and continuously run in a free air state)

· Storage Temperature ··· - 30°C to +70°C (Non-condensing)

The product can be used in an oil mist environment\*

\*Environment where machining oil mist is scattered.
Usage of this product requires an evaluation with the oil that will be used.

92×92×25mm (Mass: 120q) 9WFtype







Model No.	Rated Voltage	d Voltage Operating Voltage Range Rated Current Rated Input		Rated Speed	Max. Airflow		Max. Static Pressure		SPL	Operating Temperature	Expected Life	
	[V]	[V]	[A]	[W]	[min <sup>-1</sup> ]	[m³/min]	[CFM]	[Pa]	[inchH20]	[dB(A)]	[°C]	[h]
9WF0924H401	24	20.4 to 27.6	0.13	3.12	3,900	1.45	51.2	66	0.26	42.5	-20 to +70	40,000


Some models can also be equipped without sensors as an option. Please refer to the index (pp. 417 to 437).

#### Dimensions (unit:mm)



### Reference Dimension of Mounting Holes and Vent Opening (unit: mm)











## Options (unit:mm)


Finger Guards Color Model: 109-099C Surface treatment: Nickel-chrome plating (silver)



Model: 109-099E Surface treatment: Nickel-chrome plating (silver)
: 109-099H : Cation electropainting (black)



### Airflow - Static Pressure Characteristics



9WF0924H401